

NORYL PPXTM RESIN PPX640

REGION AMERICAS

DESCRIPTION

NORYL PPXTM 640 resin is a 40% glass reinforced alloy of polyphenylene ether (PPE) + Polypropylene (PP). This injection moldable grade exhibits high stiffness along with temperature performance, impact resistance, hydrolytic stability, and dimensional stability. NORYL PPX640 resin is an excellent candidate for applications requiring a good chemical resistance and high stiffness.

TYPICAL PROPERTY VALUES

Revision 20190925

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
MECHANICAL			
Tensile Stress, yld, Type I, 5 mm/min	95	MPa	ASTM D 638
Tensile Stress, brk, Type I, 5 mm/min	95	MPa	ASTM D 638
Tensile Strain, brk, Type I, 5 mm/min	6.4	%	ASTM D 638
Flexural Stress, brk, 1.3 mm/min, 50 mm span	150	MPa	ASTM D 790
Flexural Modulus, 1.3 mm/min, 50 mm span	8310	MPa	ASTM D 790
IMPACT			
Izod Impact, unnotched, 23°C	576	J/m	ASTM D 4812
Izod Impact, notched, 23°C	106	J/m	ASTM D 256
Izod Impact, notched, -30°C	96	J/m	ASTM D 256
Instrumented Impact Total Energy, 23°C	16	J	ASTM D 3763
Instrumented Impact Total Energy, -30°C	14	J	ASTM D 3763
THERMAL			
Vicat Softening Temp, Rate B/50	163	°C	ASTM D 1525
HDT, 0.45 MPa, 3.2 mm, unannealed	158	°C	ASTM D 648
HDT, 1.82 MPa, 3.2mm, unannealed	146	°C	ASTM D 648
CTE, -40°C to 40°C, flow	1.08E-05	1/°C	ASTM E 831
CTE, -40°C to 40°C, xflow	6.3E-05	1/°C	ASTM E 831
PHYSICAL			
Specific Gravity	1.3	-	ASTM D 792
Mold Shrinkage, flow, 3.2 mm	0.17 – 0.18	%	SABIC method
Mold Shrinkage, xflow, 3.2 mm	0.27 – 0.61	%	SABIC method
Melt Flow Rate, 260°C/5.0 kgf	1.3	g/10 min	ASTM D 1238
FLAME CHARACTERISTICS⁽¹⁾			
UL Yellow Card Link	E121562-221228	-	-
UL Recognized, 94HB Flame Class Rating	≥1.5	mm	UL 94
INJECTION MOLDING			
Drying Temperature	65 – 75	°C	
Drying Time	2 – 4	hrs	
Drying Time (Cumulative)	8	hrs	
Maximum Moisture Content	0.02	%	
Melt Temperature	260 – 305	°C	
Nozzle Temperature	260 – 305	°C	
Front - Zone 3 Temperature	255 – 300	°C	

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
Middle - Zone 2 Temperature	250 – 290	°C	
Rear - Zone 1 Temperature	245 – 290	°C	
Mold Temperature	40 – 65	°C	
Back Pressure	0.3 – 0.7	MPa	
Screw Speed	20 – 100	rpm	
Shot to Cylinder Size	30 – 70	%	
Vent Depth	0.051 – 0.076	mm	

(1) UL Ratings shown on the technical datasheet might not cover the full range of thicknesses and colors. For details, please see the UL Yellow Card.

DISCLAIMER

Any sale by SABIC, its subsidiaries and affiliates (each a "seller"), is made exclusively under seller's standard conditions of sale (available upon request) unless agreed otherwise in writing and signed on behalf of the seller. While the information contained herein is given in good faith, SELLER MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING MERCHANTABILITY AND NONINFRINGEMENT OF INTELLECTUAL PROPERTY, NOR ASSUMES ANY LIABILITY, DIRECT OR INDIRECT, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OR PURPOSE OF THESE PRODUCTS IN ANY APPLICATION. Each customer must determine the suitability of seller materials for the customer's particular use through appropriate testing and analysis. No statement by seller concerning a possible use of any product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right.