







LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H5	HOUSING MATERIAL DETAIL CORRECTED	05DEC2014	PS	JK



RECOMMENDED PC BOARD LAYOUT



282832-4 AS SHOWN

- ① MATERIALS AND FINISH:
HOUSING: PA 4T, UL 94-V0, COLOR GREEN
TERMINAL: BRASS, PLATING: SEE TABLE.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- ⑥ NOT CUMULATIVE TOLERANCE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F. ZANOLINI 14AUG2001 CHR D. BIEVENOUR 14AUG2001 APVD D. BIEVENOUR 14AUG2001		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±.25 2 PLC ±.3 3 PLC ±.3 4 PLC ±.3 FINISH ±2		NAME TERMINAL BLOCK PIN HEADER UNSHROUDED 5.0 mm PITCH	
		PRODUCT SPEC 108-20166		SIZE CAGE CODE DRAWING NO A200779 C-282832	
MATERIAL 		WEIGHT -		RESTRICTED TO -	
		Customer Drawing		SCALE 4:1 SHEET OF REV H5	