


1 Amp. Glass Passivated Junction Rectifier

Dimensions in mm. DO-15 (Plastic)  Mounting instructions 1. Min. distance from body to soldering point, 4 mm. 2. Max. solder temperature, 350 °C. 3. Max. soldering time, 3.5 sec. 4. Do not bend lead at a point closer than 2 mm. to the body.	Voltage 50 to 1000 V. Current 1.0 A. at 70 °C.  • Glass passivated junction • High current capability • The plastic material carries U/L recognition 94 V-0 • Terminals: Axial Leads • Polarity: Color band denotes cathode
---	---

Maximum Ratings, according to IEC publication No. 134


		BYW27 50	BYW27 100	BYW27 200	BYW27 400	BYW27 600	BYW27 800	BYW27 1000
V_{RRM}	Peak recurrent reverse voltage (V)	50	100	200	400	600	800	1000
$I_{F(AV)}$	Forward current at $T_{amb} = 70\text{ °C}$	1 A						
I_{FRM}	Recurrent peak forward current	10 A						
I_{FSM}	10 ms. peak forward surge current	50 A						
T_j	Operating temperature range	– 65 to + 175 °C						
T_{stg}	Storage temperature range	– 65 to + 175 °C						
E_{RSM}	Maximum non repetitive peak reverse avalanche energy. $I_R = 0.5\text{ A}$; $T_j = 25\text{ °C}$	20 mJ						

Electrical Characteristics at $T_{amb} = 25\text{ °C}$


V_F	Max. forward voltage drop at $I_F = 1\text{ A}$	1 V
I_R	Max. reverse current at V_{RRM} at 25 °C at 100 °C	200 nA 15 $\mu\text{ A}$
R_{thj-a}	Max. thermal resistance ($l = 10\text{ mm.}$)	60 °C/W

Rating and Characteristic Curves


TYPICAL FORWARD CHARACTERISTIC



FORWARD CURRENT DERATING CURVE



MAXIMUM NON REPETITIVE
PEAK FORWARD SURGE CURRENT



TYPICAL JUNCTION CAPACITANCE

