

Circuit Breaker for Equipment thermal and thermal-magnetic, Rocker actuation, 2 pole



Non-illuminated  
black  
with magnet module



illuminated  
Green transparent  
White, lettered



Non-illuminated  
white

See below:

### Approvals and Compliances

#### Description

- Circuit breaker thermal and thermal-magnetic
- 2-pole
- Snap-in version
- Positively trip-free release
- Method of operation acc. to IEC: S-type
- Different rocker colours
- Wide current range

#### Unique Selling Proposition

- Magnetic Release for short-circuit protection
- Finely graded rated currents
- High configurability (rocker colours, lettering, illumination)
- IP65 with optional cover

#### Applications

- Power tools
- Medical and laboratory equipment
- Industrial appliances
- Equipment for construction
- Cleaning equipment
- Commercial and household kitchen appliances
- Industrial Power
- Industrial lighting arrays

#### Other versions on request

- White front cover

#### Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Detailed request for product](#), [Product News](#)

#### Technical Data

|                                        |                                                                                                                                                                                  |
|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated Voltage AC                       | IEC: 240 VAC<br>UL/CSA : 277 VAC                                                                                                                                                 |
| Rated Voltage DC                       | 60 VDC                                                                                                                                                                           |
| Rated current range AC                 | 0.05 - 20 A / Magnetic up to 16 A                                                                                                                                                |
| Conditional short circuit capacity Inc | IEC 60934: 0.05...20 A: 2 kA, SC (C1)<br>@ 240 VAC                                                                                                                               |
| Degree of Protection                   | front side IP40 acc. to IEC 60529                                                                                                                                                |
| Dielectric Strength                    | 50Hz: > 2.5 kV<br>Impulse 1.2/50 µs: > 4 kV                                                                                                                                      |
| Insulation Resistance                  | 500 VDC > 100 MΩ                                                                                                                                                                 |
| Lifetime                               | mechanical: 50'000 switching cycles<br>AC: 1.0 x I <sub>r</sub> , cos φ 0.6:<br>50'000 switching cycles<br>DC: 1.0 x I <sub>r</sub> , L/R = 2 - 3 ms:<br>50'000 switching cycles |

|                           |                                                                                                                          |
|---------------------------|--------------------------------------------------------------------------------------------------------------------------|
| Overload                  | IEC: min. 40 trips<br>@ 6 x I <sub>r</sub> , cos φ 0.6<br>UL / CSA: min. 50 trips<br>@ 1.5 x I <sub>r</sub> , cos φ 0.75 |
| Allowable Operation Temp. | -30°C to 60°C                                                                                                            |
| Storage Temperature       | -40°C to 60°C                                                                                                            |
| Vibration Resistance      | ± 0.75 mm @ 10 - 60 Hz<br>acc. to IEC 60068-2-6, test Tc<br>10 G @ 60 - 500 Hz<br>acc. to IEC 60068-2-6, test Tc         |
| Shock Resistance          | 30 G / 18ms<br>acc. to IEC 60068-2-27, test Ea                                                                           |
| Tripping Type             | Thermal                                                                                                                  |
| Possible Tripping Types   | Thermal-Magnetic                                                                                                         |
| Actuation Type            | Rocker                                                                                                                   |
| Weight                    | 32 g - magnetic 56 g                                                                                                     |

#### Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

## Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: TA35

| Approval Logo                                                                    | Certificates                  | Certification Body | Description                              |
|----------------------------------------------------------------------------------|-------------------------------|--------------------|------------------------------------------|
|  | <a href="#">VDE Approvals</a> | VDE                | VDE Certificate Number: 40019754         |
|  | <a href="#">UL Approvals</a>  | UL                 | UR File Number: E71572                   |
|  | <a href="#">CCC Approvals</a> | CCC                | CCC Certificate Number: 2024010307676639 |

## Product standards

Product standards that are referenced

| Organization                                                                     | Design                | Standard          | Description                                                           |
|----------------------------------------------------------------------------------|-----------------------|-------------------|-----------------------------------------------------------------------|
|  | Designed according to | IEC 60934         | Circuit-breakers for equipment (CBE)                                  |
|  | Designed according to | UL 1077           | Standard for Supplementary Protectors for Use in Electrical Equipment |
|  | Designed according to | CSA C22.2 No. 235 | Supplementary Protectors                                              |
|  | Designed according to | GB 17701          | Circuit-breaker for equipment                                         |

## Application standards

Application standards where the product can be used


| Organization                                                                      | Design                         | Standard       | Description                                                                                   |
|-----------------------------------------------------------------------------------|--------------------------------|----------------|-----------------------------------------------------------------------------------------------|
|  | Suitable for applications acc. | IEC/UL 62368-1 | Audio/video, information and communication technology equipment - Part 1: Safety requirements |

## Compliances


The product complies with following Guide Lines

| Identification                                                                     | Details                                        | Initiator   | Description                                                                                                                                                                                           |
|------------------------------------------------------------------------------------|------------------------------------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | <a href="#">CE declaration of conformity</a>   | SCHURTER AG | The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008. |
|  | <a href="#">UKCA declaration of conformity</a> | SCHURTER AG | The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.                                                  |
|  | <a href="#">RoHS</a>                           | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863                                                                                                                                                    |
|  | <a href="#">China RoHS</a>                     | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.                                                                                  |
|  | <a href="#">REACH</a>                          | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.                               |


Dimension [mm]




TA35 without protection cover




TA35 with factory mounted transparent protection cover CZM21, IP65




TA35 with factory mounted transparent protection cover and raised collar CZM23, IP65



TA35 with factory mounted raised collar CZM24, IP40




TA35 with factory mounted transparent antibacterial protection cover CZM25, IP65



TA35 1- and 2-pole protected


## Diagrams

1-pole thermal protected, illuminated




1) Line, 2) Load  
 Codepos AAA = C12, C14, C17, C18, C19

1-pole thermal protected, non illuminated




1) Line, 2) Load

2-pole thermal protected, illuminated




1) Line, 2) Load  
 Codepos AAA = C32, C34, C37, C38, C39

2-pole thermal protected, non illuminated




1) Line, 2) Load


1-pole thermal and magnetic protected, illuminated




1-pole thermal and magnetic protected, non illuminated



2-pole thermal and magnetic protected, illuminated



2-pole thermal and magnetic protected, non illuminated



The keys / codepos are listed in the key table of the basic function for selection.

| Approval                                                                          |               | Rated current | Rated Voltage AC | Rated Voltage DC |
|-----------------------------------------------------------------------------------|---------------|---------------|------------------|------------------|
|  | UL 1077       | 0.05...20 A   | 277 V            | 32/60 V          |
|                                                                                   | CSA C22.2 235 | 0.05...20 A   | 277 V            | 32/60 V          |
|                                                                                   | IEC 60934     | 0.05...20 A   | 240 V            | 32/60 V          |
|                                                                                   | GB 17701      | 0.05...20 A   | 240 V            | 60 V             |

## Typical internal resistance per pole

| Rated Current [A] | Internal Resistance [ $\Omega$ ] |
|-------------------|----------------------------------|
| 0.05              | 200.000                          |
| 0.1               | 70.000                           |
| 0.5               | 2.750                            |
| 1.0               | 0.720                            |
| 1.5               | 0.340                            |
| 2.0               | 0.187                            |
| 2.5               | 0.115                            |
| 2.8               | 0.089                            |
| 3.0               | 0.059                            |
| 4.0               | 0.059                            |
| 5.0               | 0.044                            |
| 6.0               | 0.028                            |
| 7.0               | 0.0142                           |
| 8.0               | 0.0142                           |
| 10.0              | 0.0109                           |
| 12.0              | 0.0086                           |
| 13.0 *            | 0.0072                           |
| 14.0 *            | 0.0072                           |
| 15.0 *            | 0.0056                           |
| 16.0 *            | 0.0056                           |
| 18.0 *            | 0.0052                           |
| 20.0 *            | 0.0052                           |

\* 3-Pole max. 12 A

## Effect of ambient temperature


The units are calibrated for an ambient temperature of +23°C. To determine the rated current for a lower or higher ambient temperature, use a correction factor (typical value) from the table below:

| Ambient Temperature [°C] | Correction factor |
|--------------------------|-------------------|
| -30                      | 0.76              |
| -20                      | 0.81              |
| 0                        | 0.90              |
| +23                      | 1.00              |
| +40                      | 1.03              |
| +50                      | 1.04              |
| +60                      | 1.06              |

Example: Rated current = 5 A, Environmental temperature = 50 °C --> Correction factor = 1.04, Resulting current = 5.2 A --> Round to next higher rated current: 6 A

Time-Current-Curves


Tripping Characteristics thermal  $I_n < 3\text{ A}$



Multiple of Rated Current  $I_n$

Ambient temperature +23°


Tripping Characteristics thermal  $I_n \geq 3 \dots \leq 15\text{ A}$



Multiple of Rated Current  $I_n$

Ambient temperature +23°


Tripping Characteristics thermal magnetic fast acting



Multiple of Rated Current  $I_n$

Ambient temperature +23°

Tripping Characteristics thermal magnetic time lag



Multiple of Rated Current  $I_n$

Ambient temperature +23°

|   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| T | A | 3 | 5 | - | C | B | D | W | F | Z | 0 | 5 | C | 0 | - | 0 | 0 | 0 | - | C | Z | M | 2 | 1 |
|   |   |   |   |   |   |   |   | 1 |   | 2 | 3 | 4 |   | 5 |   |   |   |   | 6 |   | 7 |   |   |   |



1

\* grey highlighted fields: configuration is not offered anymore



2

| Front Bezel | Rocker without illumination | Rocker with illumination |   |   |
|-------------|-----------------------------|--------------------------|---|---|
| black       | -                           | clear transparent        | = | 1 |
| black       | -                           | red transparent          | = | 3 |
| black       | -                           | green transparent        | = | 4 |
| black       | -                           | orange transparent       | = | 6 |
| black       | -                           | blue transparent         | = | 7 |
| black       | black                       | -                        | = | B |
| black       | green                       | -                        | = | G |
| black       | red                         | -                        | = | R |
| black       | white                       | -                        | = | W |
| black       | orange                      | -                        | = | X |
| black       | yellow                      | -                        | = | Y |

10 | SCHURTER | Circuit Breakers

| Special marking                     |   |  | 6 |
|-------------------------------------|---|-------------------------------------------------------------------------------------|---|
| Standard                            | = | 000                                                                                 |   |
| Special marking (XXX = placeholder) | = | XXX                                                                                 |   |

Transparent antibacterial protection cover, 2-pole, IP65  = CZM25

## Variants

| Basic function                              | Rocker colour     | Legend        | Rated current | Accessories                                | Config. Code              | Order Number |
|---------------------------------------------|-------------------|---------------|---------------|--------------------------------------------|---------------------------|--------------|
| 2-pole, 2 bimetal, without illumination     | White             | embossed      | 3.0 A         | Without cover                              | TA35-CBDWF030C0-000       | 4435.0022    |
| 2-pole, 2 bimetal, without illumination     | White             | black printed | 3.0 A         | Without cover                              | TA35-CBDWM030C0-000       | 4435.0374    |
| 2-pole, 2 bimetal, without illumination     | Black             | white printed | 4.0 A         | Without cover                              | TA35-CBDH040C0-000        | 4435.0276    |
| 2-pole, 2 bimetal, without illumination     | White             | embossed      | 5.0 A         | Without cover                              | TA35-CBDWF050C0-000       | 4435.0039    |
| 2-pole, 1 bimetal, without illumination     | White             | embossed      | 6.0 A         | Without cover                              | TA35-CBTWF060C0-000       | 4435.0042    |
| 2-pole, 2 bimetal, illuminated 240 V        | Green transparent | white printed | 6.0 A         | Without cover                              | TA35-C324H060C0-000       | 4435.0265    |
| 2-pole, 1 bimetal, without illumination     | White             | embossed      | 8.0 A         | Without cover                              | TA35-CBTWF080C0-000       | 4435.0046    |
| 2-pole, 1 bimetal, without illumination     | Black             | white printed | 8.0 A         | Without cover                              | TA35-CBTBL080C0-000       | 4435.0067    |
| 2-pole, 2 bimetal, illuminated 240 V        | Blue transparent  | white printed | 8.0 A         | Transparent cover, IP65                    | TA35-C327L080C0-000-CZM21 | 4435.0483    |
| 2-pole, 1 bimetal, without illumination     | Black             | white printed | 10.0 A        | Without cover                              | TA35-CBTBL100C0-000       | 4435.0012    |
| 2-pole, 1 bimetal, without illumination     | White             | embossed      | 10.0 A        | Without cover                              | TA35-CBTWF100C0-000       | 4435.0047    |
| 2-pole, 2 bimetal, without illumination     | White             | black printed | 10.0 A        | Without cover                              | TA35-CBDWM100C0-000       | 4435.0091    |
| 2-pole, 1 bimetal, illuminated 240 V        | Green transparent | embossed      | 10.0 A        | Without cover                              | TA35-C124F100C0-000       | 4435.0187    |
| 2-pole, 2 bimetal, without illumination     | White             | embossed      | 10.0 A        | Without cover                              | TA35-CBDWF100C0-000       | 4435.0195    |
| 2-pole, 2 bimetal, w/o illum., magnetic T2  | White             | black printed | 10.0 A        | Without cover                              | TA35-CBDWM100T2-000       | 3-150-705    |
| 2-pole, 2 bimetal, w/o illum., magnetic F2  | White             | black printed | 10.0 A        | Without cover                              | TA35-CBDWM100F2-000       | 3-150-706    |
| 2-pole, 2 bimetal, without illumination     | White             | embossed      | 12.0 A        | Without cover                              | TA35-CBDWF120C0-000       | 4435.0304    |
| 2-pole, 2 bimetal, without illumination     | Black             | embossed      | 15.0 A        | Without cover                              | TA35-CBDBF150C0-000       | 4435.0347    |
| 2-pole, 2 bimetal, without illumination     | White             | black printed | 15.0 A        | Raised collar with transparent cover, IP65 | TA35-CBDWM150C0-000-CZM23 | 4435.0423    |
| 2-pole, 2 bimetal, w/o illum., magnetic F2  | White             | embossed      | 16.0 A        | Without cover                              | TA35-CBDWF160F2-000       | 3-147-647    |
| 2-pole, 2 bimetal, illuminated, magnetic F2 | Green transparent | embossed      | 16.0 A        | Without cover                              | TA35-C324F160F2-000       | 3-150-707    |
| 2-pole, 2 bimetal, illuminated, magnetic T2 | Green transparent | embossed      | 16.0 A        | Without cover                              | TA35-C324F160T2-000       | 3-150-708    |
| 2-pole, 1 bimetal, without illumination     | White             | embossed      | 20.0 A        | Without cover                              | TA35-CBTWF200C0-000       | 4435.0002    |
| 2-pole, 2 bimetal, without illumination     | White             | embossed      | 20.0 A        | Without cover                              | TA35-CBDWF200C0-000       | 4435.0013    |
| 2-pole, 2 bimetal, without illumination     | Black             | white printed | 20.0 A        | Without cover                              | TA35-CBDL200C0-000        | 4435.0321    |

Availability for all products can be searched real-time: <https://www.schurter.com/en/info-center/support-tools/stock-check-distributors>

## Packaging Unit

10 Pcs

## Accessories

## Description



TA35\_Accessories  
Screw-on collar with cover, IP65