



Glass Passivated Rectifier Diode Modules


VRRM 800 to 1800V
IFAV 200 Amp

Applications

- Non-controllable rectifiers for AC/AC converters
- Line rectifiers for transistorized AC motor controllers
- Field supply for DC motors

Features

- Blocking voltage: 800 to 1800V
- Heat transfer through aluminum oxide ceramic isolated metal baseplate
- Glass passivated chip
- UL E243882 approved



Module Type

TYPE			VRRM	VRS
MSCD200-08	MSAD200-08	MSKD200-08	800V	900V
MSCD200-12	MSAD200-12	MSKD200-12	1200V	1300V
MSCD200-16	MSAD200-16	MSKD200-16	1600V	1700V
MSCD200-18	MSAD200-18	MSKD200-18	1800V	1900V

Maximum Ratings

Symbol	Conditions	Values	Units
IFAV	Single phase ,half wave 180° conduction Tc=95℃	200	A
IF(RMS)	Single phase ,half wave 180° conduction Tc=102℃	240	A
IFSM	t=10mS Tvj =45℃	6800	A
i ² t	t=10mS Tvj =45℃	231200	A ² s
Vsol	a.c.50HZ;r.m.s.;1min	3000	V
Tvj		-40 to 150	℃
Tstg		-40 to 125	℃
Mt	To terminals(M6)	5±15%	Nm
Ms	To heatsink(M6)	5±15%	Nm
Weight	Module (Approximately)	160	g

Thermal Characteristics

Symbol	Conditions	Values	Units
Rth(j-c)	Per diode	0.18	℃/W
Rth(c-s)	Module	0.05	℃/W

Electrical Characteristics

Symbol	Conditions	Values			Units
		Min.	Typ.	Max.	
VFM	T=25℃ IF =300A	—	1.18	1.30	V
IRD	Tvj=150℃ VRD=VRRM	—	—	9	mA

Performance Curves




Fig1. Power dissipation




Fig2. Forward Current Derating Curve




Fig3. Transient thermal impedance




Fig4. Max Non-Repetitive Forward Surge Current





Fig5. Forward Characteristics

Package Outline Information

CASE: D2



Dimensions in mm