

**620-002**  
**Strain Relief**  
**Stainless Steel - Rotatable Coupling - 90°**





62

**STAINLESS STEEL**

**CONNECTOR  
DESIGNATOR**

**A**

**ROTATABLE  
COUPLING**



See inside back cover fold-out or page 14 for Table I.

**TABLE III: CABLE ENTRY**

| Shell Size | E Max        | F Max        | G Max        | H Max      | Cable Entry |              |
|------------|--------------|--------------|--------------|------------|-------------|--------------|
|            |              |              |              |            | Closed      | Open         |
| 08         | .704 (17.9)  | .808 (20.5)  | .752 (19.1)  | .125 (3.2) | .125 (3.2)  | .204 (5.2)   |
| 10         | .786 (20.0)  | .867 (22.0)  | .832 (21.1)  | .125 (3.2) | .187 (4.7)  | .286 (7.3)   |
| 12         | .979 (24.9)  | .929 (23.6)  | .988 (25.1)  | .188 (4.8) | .291 (7.4)  | .416 (10.6)  |
| 14         | 1.039 (26.4) | .992 (25.2)  | 1.046 (26.6) | .188 (4.8) | .351 (8.9)  | .476 (12.1)  |
| 16         | 1.188 (30.2) | 1.056 (26.8) | 1.319 (33.5) | .188 (4.8) | .501 (12.7) | .626 (15.9)  |
| 18         | 1.300 (33.0) | 1.233 (31.3) | 1.451 (36.9) | .188 (4.8) | .518 (13.2) | .706 (17.9)  |
| 20         | 1.425 (36.2) | 1.296 (32.9) | 1.551 (39.4) | .188 (4.8) | .581 (14.8) | .831 (21.1)  |
| 22         | 1.550 (39.4) | 1.358 (34.5) | 1.653 (42.0) | .188 (4.8) | .644 (16.4) | .956 (24.3)  |
| 24         | 1.675 (42.5) | 1.420 (36.1) | 1.775 (45.1) | .188 (4.8) | .706 (17.9) | 1.081 (27.5) |
| 28         | 1.813 (46.1) | 1.634 (41.5) | 2.020 (51.3) | .188 (4.8) | .750 (19.1) | 1.187 (30.1) |

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.