

# PC Board Fuses - Sub Miniature with Leads

## GFA, GLN and GLX Series



**Catalog Symbol:** GFA

**Sub Miniature with Axial Leads**

**Non Time-Delay**

0.145" x 0.300" (3.7mm x 7.6mm)

**Interrupting Rating:** 50 AIC

**Agency Approvals:**

UL Recognized, (1/2-5A) Guide JDYZ2, File 19180

CSA Certified, (1/2-5A) File 53787, Class 1425-01



**Catalog Symbol:** GLN

**Sub Miniature with Radial Leads**

**Non Time-Delay**

0.145" x 0.300" (3.7mm x 7.6mm)

**Interrupting Rating:** 50 AIC

**Electrical Ratings (Catalog Symbol and Amps)**

**125 Volts AC**

Amps	Test Spec.	Color Code (Opp. Ends)	Amps	Test Spec.	Color Code (Opp. Ends)
GFA-1/200	A	Red Blk	GFA-3/10	A	Grn Grn
GFA-1/100	A	Red Orn	GFA-3/10	A	Blu Blu
GFA-1/64	A	Red Grn	GFA-1/2	B	Orn Grn
GFA-1/50	A	Red Wht	GFA-3/10	B	Orn Blu
GFA-1/32	A	Red Brn	GFA-3/10	B	Orn Pur
GFA-1/20	A	Yel Yel	GFA-1	B	Yel Grn
GFA-1/16	A	Brn Brn	GFA-1 1/2	B	Yel Pur
GFA-1/10	A	Red Red	GFA-2	B	Grn Blu
GFA-1/8	A	Orn Orn	GFA-2 1/2	B	Grn Brn
GFA-1 1/2	B	Red Yel	GFA-3	B	Blu Pur
GFA-3/10	B	Red Blu	GFA-4	B	Pur Brn
GFA-1/4	B	Red Pur	GFA-5	B	Brn Blk

**32 Volts AC**

Amps	Test Spec.	Color Code (Opp. Ends)	Amps	Test Spec.	Color Code (Opp. Ends)
GFA-7	A	Pur Grn	GFA-12	A	Blk Blu
GFA-8	A	Grn Blk	GFA-15	A	Blk Pur
GFA-10	A	Yel Brn	—	—	—

**Test Specifications**

**Wire Lead Size**

Load	Opening Time		No.	Fuse
	"A"	"B"		
100%	4 hrs. (min.)	—	24	1/200 to 5A
150%	—	10 sec. (max.)	18	6 to 10A
200%	10 sec.	—	16	15A

**Carton Quantity and Weight**

Amp Ratings	Carton Qty.	Weight*
		Lbs. Kg.
1/200-15	100	0.171 52.6

\*Weight per carton.

**General Information:**

- Glass tube fuses for protection of subminiature devices.
- Tinned wire leads solder into circuit.
- Withstand high-shock and vibration.
- Color-coded for amp rating.
- Axial leads (1 1/2") can be fed through wire forming machine.

**Carton Quantity and Weight**

Amp Ratings	Carton Qty.	Weight*
		Lbs. Kg.
1/200-10	100	0.171 52.6


\*Weight per carton.

**General Information:**

- Glass tube fuses for protection of subminiature devices.
- Tinned radial leads spaced for easy assembly on printed circuit chassis.
- Withstand high-shock and vibration.
- Color-coded for amp rating.
- Radial leads (1 1/2") can be fed through wire forming machine.

# PC Board Fuses - Sub Miniature with Leads

## GFA, GLN and GLX Series



**Catalog Symbol:** GLX

**Sub Miniature with Radial Leads**

**Non-Time-Delay**

0.145" x 0.300" (3.7mm x 7.6mm)

**Interrupting Rating:** 50 AIC

### Electrical Ratings (Catalog Symbol and Amps)

**125 Volts AC**

Amps	Test Spec.	Color Code (Opp. Ends)	Amps	Test Spec.	Color Code (Opp. Ends)		
GLX-1/32	B	Red	Pur	GLX-2	B	Grn	Blu
GLX-1/20	B	Orn	Grn	GLX-3	B	Blu	Pur
GLX-1/10	B	Orn	Pur	GLX-4	B	Pur	Brn
GLX-1/8	B	Yel	Grn	GLX-5	B	Brn	Blk
GLX-1/4	B	Yel	Pur	—	—	—	—

### Wire Lead Size

No.	Fuse
24	1/200 to 5A

### Carton Quantity and Weight


Amp Ratings	Carton Qty.	Weight*	
		Lbs.	Kg.
1/4-5	100	0.171	52.6

\*Weight per carton.

### General Information:

- Glass tube fuses for protection of subminiature devices.
- Tinned radial leads spaced for easy assembly on printed circuit chassis.
- Withstand high-shock and vibration.
- Color-coded for ampere rating.
- Radial leads (1 1/2") can be fed through wire forming machine.

### Time-Current Characteristics—Total Clear



The only controlled copy of this BIF document is the electronic read-only version located on the Bussmann Network Drive. All other copies of this BIF document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[GFA-1/32](#) [GFA-3](#) [GFA-3/10](#)