

## Panel feed-through - SACC-DSIV-FSB-5CON-L180 SCOTHR - 1542635

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type socket, 5-pos., M12 SPEEDCON, B-coded, rear/screw mounting with M12 thread, with polarity protection, with straight THR solder connection



### Key commercial data

Packing unit	1 1
Minimum order quantity	60 1
Weight per Piece (excluding packing)	10.29 GRM
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

#### General

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	5
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	B - inverse
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II
Pollution degree	3

# Panel feed-through - SACC-DSIV-FSB-5CON-L180 SCOTHR - 1542635

## Technical data

### General

Connection method	THR solder connection
Mounting type	Rear mounting M12 x 1 With flat nut

### Material

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PPA
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	FKM / EPDM

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

### ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002061
ETIM 5.0	EC002061

### UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

## Approvals

### Approvals

## Panel feed-through - SACC-DSIV-FSB-5CON-L180 SCOTHR - 1542635

### Approvals

Approvals

GOST / GOST

---

Ex Approvals

---

Approvals submitted

---


### Approval details

GOST 

GOST 


### Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side


Dimensioned drawing




Housing cut-out for two-part M12 flush-type connectors  
with THR and wave soldering connection, version 1

## Panel feed-through - SACC-DSIV-FSB-5CON-L180 SCOTHR - 1542635

Dimensioned drawing




Drilling diagram




Housing cut-out for two-part M12 flush-type connectors with THR and wave soldering connection, version 2

Dimensioned drawing




Dimensioned drawing



M12 flush-type connector

Housing cutout for M12 fastening thread, mounting panel with feed-through hole (alternative with surface as protection against rotation)

Dimensioned drawing



THR tray packaging