










Energy Efficient Direct Incandescent Replacement Miniature Based Cool White LEDs

Miniature Packages	Replaces Incandescent	Part Number	Electrical-Optical Characteristics (Ta = 25°C)				Angle of Illumination	Special Features
			Voltage V typ	Current mA typ	Intensity Ft.Cd	Intensity mcd		
T3-1/4 (9mm) Miniature Bayonet  BF321	6MB, 44, 47, 755	BF321CW600-6V-BP	5/6V	15	60	160	120°	Center Contact Polarity BP = Bipolar AC/DC P = Positive N = Negative Replace BF321 With B321 for Std. Beam (50°)
	12MB, 756	BF321CW600-14V-BP	12/14V	15	60	160		
	24MB,	BF321CW600-24V-BP	24V	15	60	160		
	313,757,1819,1829	BF321CW600-28V-BP	28V	15	60	160		
	48MB	BF321CW600-48V-BP	48V	12	48	128		
	60MB,1835	BF321CW600-60V-BP	60V	12	48	128		
	120MB, NE51H	BF321CW600-120VAC	120VAC	10	40	106		
		BF321CW600-130V-BP	130V	8	32	85		
T3-1/4 (9mm) Miniature Bayonet LED Cluster  BF304	6MB, 44, 47, 755	BF304CW600-6V-BP	5/6V	60	240	640	120°	Center Contact Polarity BP = Bipolar AC/DC P = Positive N = Negative Replace BF304 With B304 for Std. Beam (50°)
	12MB, 756	BF304CW600-14V-BP	12/14V	30	240	640		
	24MB,	BF304CW600-24V-BP	24V	15	240	640		
	313,757,1819,1829	BF304CW600-28V-BP	28V	15	240	640		
	48MB	BF304CW600-48V-BP	48V	12	192	512		
	60MB,1835	BF304CW600-60V-BP	60V	12	192	512		
	120MB, NE51H	BF304CW600-120VAC	120VAC	10	160	424		
		BF304CW600-130V-BP	130V	8	128	340		
T3-1/4 (9mm) Miniature Bayonet LED Cluster  BF3127	6MB, 44, 47, 755	BF3126CW600-6V-BP	5/6V	90	300	900	120°	Center Contact Polarity BP = Bipolar AC/DC P = Positive N = Negative Replace BF3126/3127 With B3126/3127 for Std. Beam (50°)
	12MB, 756	BF3126CW600-14V-BP	12/14V	30	300	900		
	24MB,	BF3127CW600-24V-BP	24V	15	300	900		
	313,757,1819,1829	BF3127CW600-28V-BP	28V	15	300	900		
	48MB	BF3127CW600-48V-BP	48V	12	280	840		
	60MB,1835	BF3127CW600-60V-BP	60V	12	280	840		
	120MB, NE51H	BF3127CW600-120VAC	120VAC	10	230	700		
		BF3127CW600-130V-BP	130V	8	190	560		
T3-1/4 (9mm) Miniature Wedge  WF321	159,259,555,1995-7	WF321CW600-6V-BP	5/6V	15	60	160	120°	BP = Bipolar AC/DC Replace WF321 With W321 for Std. Beam (50°)
	124,658,2080,936	WF321CW600-14V-BP	12/14V	15	60	160		
	656,657,400,464,655	WF321CW600-24V-BP	24V	15	60	160		
	656,657,400,464,655	WF321CW600-28V-BP	28V	15	60	160		
		WF321CW600-48V-BP	48V	12	48	128		
		WF321CW600-120VAC	120VAC	10	40	106		
		WF321CW600-130V-BP	130V	8	32	85		
		WF321CW600-24V-BP	24V	15	60	160		
S6 Candelabra Screw Base  SLF461  SLF464  SLF467		SLF461CW600-24V-BP	24V	15	60	160	120°	Center Contact Polarity BP = Bipolar AC/DC P = Positive N = Negative Replace BF321 With B321 for Std. Beam (50°)
		SLF461CW600-120VAC	120VAC	10	40	106		
		SLF461CW600-130V-BP	130V	8	32	85		
		SLF461CW600-220VAC	220VAC	4	16	42		
		SLF464CW600-24V-BP	24V	15	240	640		
		SLF464CW600-120VAC	120VAC	10	160	424		
		SLF464CW600-130V-BP	130V	8	128	340		
		SLF464CW600-220VAC	220VAC	4	64	168		
		SLF467CW600-24V-BP	24V	15	420	1120		
		SLF467CW600-120VAC	120VAC	10	280	742		
		SLF467CW600-130V-BP	130V	8	224	595		
		SLF467CW600-220VAC	220VAC	4	112	294		

All dimensions in inches. For millimeters multiply by 25.4

Caution A white LED is sensitive to static electricity and care should be taken in handling it. When an overvoltage is applied, which exceeds the absolute maximum rating of the white LED, its energy damages the LED.

Log # 078B Rev 1-99