



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS		POWER				SIGNAL						POWER		
		E1	P1	P2	P3	1	2	3	4	5	6	P4	P5	E2	
51939-405-- NOTE 3	D C B A		PA	PA	PA	UUUUUU	TTTTTT	SSSSSS	SSSSSS	SSSSSS	SSSSSS	PA	PA		



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
HA	[N/A]	HOLD-DOWN
F	[5.59]	SIGNAL
H	[5.59]	SIGNAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date			linear	0.X ±0.5	COPY		projection		title	
A	DG09-0017	JW	12/19/08			angles	0.XX ±0.25					3ACP + 24S + 2P	
							0.XXX ±0.1					RIGHT ANGLE SOLDER HEADER	
						dr	0° ±2°					product family	PwrBlade
						enr	JULIA WANG 12/19/08					size	dwg no
						chr	JEROME CHEN 12/19/08					A	51939-405
						appd	GARY HSIEH 12/19/08					code	213
							JOSEPH HSIA 12/19/08					sheet	1 of 4
sheet index	revision sheet	A	A	A	A			scale	1:1				
		1	2	3	4								

Pro/E




cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-405-
NOTE: 3




mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.5		COPY		www.fciconnect.com		
A					0.XX ±0.25		projection	title			
					0.XXX ±0.1			3ACP + 24S + 2P			
				angles	0° ±2°			RIGHT ANGLE SOLDER HEADER			
				dr	JULIA WANG	12/19/08		product family		PwrBlade	code
				engr	JEROME CHEN	12/19/08		size		dwg no	213
				chr	GARY HSIEH	12/19/08	scale	A		51939-405	sheet
				appd	JOSEPH HSIA	12/19/08					2 of 4
sheet index		revision sheet									

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-405--
NOTE: 3



RECOMMENDED PCB LAYOUT

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear		0.X ±0.5		COPY		www.fciconnect.com	
A						0.XX ±0.25		projection		title	
						0.XXX ±0.1				3ACP + 24S + 2P	
				angles		0° ±2°		MIM		RIGHT ANGLE SOLDER HEADER	
						dr JULIA WANG 12/19/08		product family PwrBlade		code 213	
						enr JEROME CHEN 12/19/08		size		dwg no 51939-405	
						chr GARY HSIEH 12/19/08		scale 1:1		sheet 3 of 4	
						appd JOSEPH HSIA 12/19/08					
sheet index		revision sheet									

Pro/E

cage code 22526

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

4

4

3