





PRODUCT NO.
SEE TABLE



NOTES :

- ① POLARIZING KEY MUST BE COMPLETELY SEATED AGAINST THE ANGLES OF THE MALE PIN LEAD-IN.
2. PACKAGE PER BUS-14-022.
3. CSA CERTIFIED. MUST CONFORM TO BUS-22-265.
- ④ MOLDING MATERIAL : MODIFIED POLYPHENYLENE ETHER
COLOR : BLACK. MEETING UL-94V-0
5. TO BE MATED WITH PIN .230/5.84 LONG.
6. THIS HOUSING IS INTENDED FOR USE WITH BERG
MINI PV™ TERMINAL WITH 22-36 AWG WIRE.
7. FOR APPLICATION INFORMATION SEE TA-531.
- ⑧ PACKAGE EIGHT-DIGIT PART NUMBERS FOLLOWED
BY A "B" IN BULK PACKAGING PER BUS-14-022.
- ⑨ ADD AN LF SUFFIX TO PART NUMBERS FOR PRODUCT
THAT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
10. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO
MANUFACTURING SOLDER PROCESSES.



mat'l. code NOTE 4				tolerances unless otherwise specified		CUSTOMER COPY	FCI www.fciconnect.com		
ltr	ecn no	dr	date				title	product family	code
J	V31682	PDP	09/15/93	linear	.XX ±.01/.X±.3	projection	MINI LATCH HOUSING	MINI LATCH	213
K	V50128	GAH	03/21/95		.XXX ±.005/.XX±.13		POL. S.R. .100/2.54 C.C.		
L	V61656	HTB	11/07/96	angles	.XXXX ±.0020/.XXX±.051				
M	V71422	HTB	09/30/97	dr	0° ±2°	INCH/MM			
N	V90972	CGC	05/10/99	enr		scale			
P	V03-1357	PJ	02/06/04	chr	S.ROYER 08/18/88	2:1			
R	V05-0713	DAI	07/29/05	appd	J.SHUEY 08/18/88				
					J.SHUEY 08/18/88				
sheet index	revision sheet	R	R						
		1	2						

cage code
22526

A

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

FCI

A

B

PRODUCT NUMBER NOTE 9	NO. OF POSITIONS	LATCH OR POLARIZED POSITION	DIM A MAX.		DIM B		SPECIAL MARKINGS	COMMENTS	NOTE
			ENGLISH	METRIC	ENGLISH	METRIC			
65406-001	4	2	0.405	10.29	0.300	7.62		DETAIL X	
65406-002	4	3	0.405	10.29	0.300	7.62		DETAIL X	
65406-003	8	2	0.805	20.45	0.700	17.78		DETAIL X	
65406-004	8	7	0.805	20.45	0.700	17.78		DETAIL X	
65406-005	10	2	1.005	25.53	0.900	22.86		DETAIL X	
65406-006	10	9	1.005	25.53	0.900	22.86		DETAIL X	
65406-007	12	2	1.205	30.61	1.100	27.94		DETAIL X	
65406-008	12	11	1.205	30.61	1.100	27.94		DETAIL X	
65406-009	14	2	1.405	35.69	1.300	33.02		DETAIL X	
65406-010	16	2	1.605	40.77	1.500	38.10		DETAIL X	
65406-011	16	15	1.605	40.77	1.500	38.10		DETAIL X	
65406-012	20	2	2.005	50.93	1.900	48.26		DETAIL X	
65406-013	20	19	2.005	50.93	1.900	48.26		DETAIL X	
65406-014	24	2	2.405	61.09	2.300	58.42		DETAIL X	
65406-015	24	23	2.405	61.09	2.300	58.42		DETAIL X	
65406-016	5	2	0.505	12.83	0.400	10.16		DETAIL X	
65406-017	5	4	0.505	12.83	0.400	10.16		DETAIL X	
65406-018	4	2	0.405	10.29	0.300	7.62		DETAIL Y	
65406-019	4	3	0.405	10.29	0.300	7.62		DETAIL Z	8
65406-020	4	2	0.405	10.29	0.300	7.62		DETAIL Z	
65406-021	3	3	0.305	7.75	0.200	5.08		DETAIL Z	
65406-022	7	3	0.705	17.91	0.600	15.24		DETAIL Z	

mat'l. code —				tolerances unless otherwise specified				CUSTOMER COPY	A FCI www.fciconnect.com						
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.3				projection 	title MINI LATCH HOUSING POL. S.R. .100/2.54 C.C.					
R					.XXX ±.005/.XX±.13										
					.XXX ±.0020/.XXX±.051 0° ±2°										
				angles					INCH/MM 	product family MINI LATCH				code	
				dr	S.ROYER	08/18/88					size dwg no		213		
				enrg	T.HANNA	08/18/88					A 65406		sheet 2 of 2		
				chr	T.HANNA	08/18/88	scale 1:1								
				appd	T.HANNA	08/18/88									
sheet index	revision sheet														

1 | 2

3 |

4

ACAD

PDM: Rev:R

STATUS:Released

Printed: Aug 05, 2005

cage code
22526