

## Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Thermomagnetic circuit breaker, 1-pos., for DIN rail mounting

The figure shows the 10 A version

### Product Features

- ✓ Thermomagnetic circuit breakers feature a compact design, large-surface labeling options, and a double plug-in bridge shaft
- ✓ High level of system availability thanks to their reclosure function and clear status display
- ✓ Clear assignment of the relevant circuit breaker thanks to the large center labeling area



### Key commercial data

|                                      |                |
|--------------------------------------|----------------|
| Packing unit                         | 1 pc           |
| Weight per Piece (excluding packing) | 63.33 GRM      |
| Custom tariff number                 | 85362010       |
| Country of origin                    | Czech Republic |

### Technical data

#### General

|                                         |                 |
|-----------------------------------------|-----------------|
| Number of levels                        | 1               |
| Number of connections                   | 2               |
| Mounting type                           | DIN rail: 35 mm |
| Color                                   | gray            |
| Number of positions                     | 1               |
| Surge voltage category                  | II              |
| Insulating material                     | PA66            |
| Inflammability class according to UL 94 | V0              |

#### Electrical data

|           |                  |
|-----------|------------------|
| Fuse type | Automatic device |
|-----------|------------------|

# Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

## Technical data

### Electrical data

|                                                 |                                   |
|-------------------------------------------------|-----------------------------------|
| Rated surge voltage                             | 2.8 kV                            |
| Rated voltage                                   | 240 V AC (50/60 Hz)               |
|                                                 | 28 V DC                           |
|                                                 | 240 V AC (50/60 Hz)               |
|                                                 | 28 V DC                           |
| Operating voltage                               | 50 V AC ... 264 V AC (48 - 62 Hz) |
|                                                 | 5 V DC ... 30.8 V DC              |
| Rated current $I_n$                             | 5 A                               |
| Rated insulation voltage $U_i$                  | 440 V AC                          |
| Insulation resistance $R_{iso}$                 | > 100 MΩ (main contact)           |
| Required backup fuse                            | 20 A                              |
| Rated short-circuit switching capacity $I_{cn}$ | 200 A (240 V AC)                  |
|                                                 | 400 A (28 V DC)                   |
| Dielectric strength                             | 2000 V                            |
| Cycles, max.                                    | 6000 (at 1 x $I_n$ )              |
|                                                 | 50 (at 1.5 x $I_n$ )              |
|                                                 | 40 (at 6 x $I_n$ )                |
| Pollution degree                                | 2                                 |
| Surge voltage category                          | II                                |

### Dimensions

|        |         |
|--------|---------|
| Height | 85.5 mm |
| Width  | 12.3 mm |
| Depth  | 89.5 mm |

### Ambient conditions

|                                 |                        |
|---------------------------------|------------------------|
| Degree of protection            | IP40 (Actuation area)  |
|                                 | IP20 (Connection area) |
| Ambient temperature (operation) | -30 °C ... 60 °C       |

### Connection data

|                                                                            |                      |
|----------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                         | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                         | 10 mm <sup>2</sup>   |
| Conductor cross section stranded min.                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                      | 10 mm <sup>2</sup>   |
| Conductor cross section AWG/kcmil min.                                     | 24                   |
| Conductor cross section AWG/kcmil max                                      | 8                    |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 6 mm <sup>2</sup>    |

# Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

## Technical data

### Connection data

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| Conductor cross section stranded, with ferrule with plastic sleeve min.                 | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.                 | 6 mm <sup>2</sup>    |
| 2 conductors with same cross section, solid min.                                        | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.                                        | 2.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded min.                                     | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded max.                                     | 2.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 4 mm <sup>2</sup>    |
| Connection method                                                                       | Screw connection     |
| Stripping length                                                                        | 10 mm                |
| Screw thread                                                                            | M4                   |
| Tightening torque, min                                                                  | 1.5 Nm               |
| Tightening torque max                                                                   | 1.8 Nm               |

### Standards and Regulations

|                          |                  |
|--------------------------|------------------|
| Standards/specifications | EN 60934         |
|                          | UL 1077          |
|                          | CSA 22.2 No. 235 |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141116 |
| eCl@ss 4.1 | 27141116 |
| eCl@ss 5.0 | 27141116 |
| eCl@ss 5.1 | 27141116 |
| eCl@ss 6.0 | 27141116 |
| eCl@ss 7.0 | 27141116 |
| eCl@ss 8.0 | 27141116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000899 |
| ETIM 3.0 | EC000899 |

## Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000899 |
| ETIM 5.0 | EC000899 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121411 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121411 |

### Approvals

#### Approvals



#### Approvals

CSA / UL Recognized / VDE Zeichengenehmigung / cUL Recognized / cULus Recognized

#### Ex Approvals

#### Approvals submitted

#### Approval details



## Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

### Approvals

cUL Recognized 

cULus Recognized 

### Accessories

#### Accessories

##### Bridge

Plug-in bridge - FBS 2-6 - 3030336



Plug-in bridge, Number of positions: 2, Color: red

Plug-in bridge - FBS 3-6 - 3030242



Plug-in bridge, Number of positions: 3, Color: red

Plug-in bridge - FBS 4-6 - 3030255



Plug-in bridge, Number of positions: 4, Color: red

## Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

### Accessories

Plug-in bridge - FBS 5-6 - 3030349



Plug-in bridge, Number of positions: 5, Color: red

---

Plug-in bridge - FBS 10-6 - 3030271



Plug-in bridge, Number of positions: 10, Color: red

---

Plug-in bridge - FBS 20-6 - 3030365



Plug-in bridge, Number of positions: 20, Color: red

---

### Screwdriver tools

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

---

### Terminal marking

Marker for terminal blocks - UC-TM 12 - 0819194



Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 12 mm, Lettering field: 11.45 x 10.5 mm

# Thermomagnetic device circuit breaker - UT 6-TMC M 5A - 0916607

## Accessories

Zack marker strip - ZB 12:UNPRINTED - 0812120



Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 12.2 mm, Lettering field: 12 x 10.5 mm

Warning label printed


Warning label - WS UT 6 - 3047345



Warning sign for UT terminal blocks

## Drawings

Diagram



Trigger characteristic