



REV.	DATE	DESCRIPTION
NC	07/18/01	INITIAL RELEASE
A	05/17/05	UPDATE DRAWING FORMAT




RECOMMENDED
CABLE STRIPPING DIM'S




RECOMMENDED
MOUNTING HOLE




8 HEX NUT



Ø6.50 [Ø.256]
Ø10.20 [Ø.402]



1/4-36UNS-2A



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .118"
3. MAX. PANEL THICKNESS = 3.2mm

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.					05/17/05	
7						CHECKED			PART DESCRIPTION SMA BULKHEAD CRIMP JACK (FOR BELDEN 9913, 9914, LMR-400)				
6	FERRULE	COPPER	GOLD	1		ISSUED							
5	HEX NUT	BRASS	GOLD	1		SHEET	1 OF 1		PART NO. 132333				
4	LOCK WASHER	BRASS	GOLD	1	CAD FILE C:/132/132333.DWG			DWG. NO.					132333.DWG
3	CONTACT PIN	BRASS	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY									