




MARKETING SALES DRAWING
 DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
 DIMENSIONS IN METRIC - []

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4300-002.
 TUSONIX RoHS COMPLIANT PART NUMBER: 4300-002 LF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS PART
 NUMBER WHEN ORDERING.
- RoHS COMPLIANT PART MARKED WITH DARK GREEN DOT
 FOR IDENTIFICATION.

Cx (pF)		TOL.	DC WORKING VOLTAGE		CURRENT	IR (MIN.) @ 100 VDC	DWV	MIN. NO LOAD INSERTION LOSS (dB) @ 25° C PER MIL-STD-220					COLOR CODE
			+85°C	+125°C				1 MHz	10 MHz	100 MHz	1GHz	10 GHz	
1200		GMV	300	200	5 A	10 G	500 VDC	---	5	20	35	45	WHITE

REVISION RECORD Original Release C.O. 4984 RDN TO COMP FMP. STYLE DWG SPLIT FOR EACH VAR. S.M. 06-19-02 20020604-3-03 ADDED NOTES 1 & 2. S.M. 05-23-05 20050511-2-08	0		--TOLERANCES-- Unless Otherwise Specified		Title SOLDER MOUNT EMI FILTER		
			DECIMAL ±				
			ANGLES ±		Drawn S.M. 06-19-02		Scale 5 X
			TUSONIX TUCSON, ARIZONA		Approved J.Mc. 06-19-02		
	A				4300-002		