

## DIODE MODULE (F.R.D.)

# FDS100CA100/120



UL;E76102 (M)

**FDS100CA** is a high speed (fast recovery) diode module designed for high power switching application. **FDS100CA** is suitable for high frequency application requiring low loss and high speed control.

- High Speed  $t_{rr} \leq 300\text{ns}$
- $I_{F(AV)}$  100A (each device)
- Isolated mounting construction.
- High Surge Capability

### (Applications)

Switching Power Supply. Inverter Welding Power Supply  
Power Supply for Telecommunication



### Maximum Ratings

( $T_j = 25^\circ\text{C}$  unless otherwise specified)

| Symbol    | Item                            | Ratings     |             | Unit |
|-----------|---------------------------------|-------------|-------------|------|
|           |                                 | FDS100CA100 | FDS100CA120 |      |
| $V_{RRM}$ | Repetitive Peak Reverse Voltage | 1000        | 1200        | V    |
| $V_R(DC)$ | D.C. Reverse Voltage            | 800         | 960         | V    |

| Symbol    | Item                                 | Conditions                                            | Ratings                           | Unit                 |
|-----------|--------------------------------------|-------------------------------------------------------|-----------------------------------|----------------------|
| $I_F$     | Forward Current                      | D.C. $T_c = 78^\circ\text{C}$                         | 100                               | A                    |
| $I_{FSM}$ | Surge Forward Current                | $\frac{1}{2}$ cycle, 60Hz, peak value, non-repetitive | 2000                              | A                    |
| $I^2t$    | $I^2t$                               | Value for one cycle of surge current                  | 16600                             | $\text{A}^2\text{S}$ |
| $T_j$     | Operating Junction Temperature       |                                                       | $-40$ to $+150$                   | $^\circ\text{C}$     |
| $T_{stg}$ | Storage Temperature                  |                                                       | $-40$ to $+125$                   | $^\circ\text{C}$     |
| $V_{iso}$ | Isolation Breakdown Voltage (R.M.S.) | A.C. 1 minute                                         | 2500                              | V                    |
|           | Mounting Torque                      | Mounting (M6)                                         | Recommended Value 2.5-3.9 (25-40) | 4.7 (48)             |
|           |                                      | Terminal (M5)                                         | Recommended Value 1.5-2.5 (15-25) | 2.7 (28)             |
|           | Mass                                 | Typical Value                                         | 170                               | g                    |

### Electrical Characteristics

| Symbol        | Item                            | Conditions                                               | Ratings |      |      | Unit                      |
|---------------|---------------------------------|----------------------------------------------------------|---------|------|------|---------------------------|
|               |                                 |                                                          | Man.    | Typ. | Max. |                           |
| $I_{RRM}$     | Repetitive Peak Reverse Current | $V_R = V_{RRM}$ , $T_j = 150^\circ\text{C}$              |         |      | 5.0  | mA                        |
| $V_{FM}$      | Forward Voltage Drop            | $I_F = 100\text{A}$ , Inst. measurement                  |         |      | 1.8  | V                         |
| $t_{rr}$      | Reverse Recovery Time           | $I_F = 100\text{A}$ , $-di/dt = 100\text{A}/\mu\text{s}$ |         |      | 300  | ns                        |
| $R_{th(j-c)}$ | Thermal Impedance               | Junction to case                                         |         |      | 0.4  | $^\circ\text{C}/\text{W}$ |

