


ONE PLACE DECIMALS $\pm .1[2.5]$ THREE PLACE DECIMALS $\pm .005[.127]$
TWO PLACE DECIMALS $\pm .01[.25]$ FOUR PLACE DECIMALS $\pm .0020[.051]$

ANGLES
 $\pm 2^\circ$

TITLE:
2MM SOCKET
STRIP ASSEMBLY



DWG NO:
SQW-1XX-XX-XXX-X-XXX

SHEET 1 OF 1



SECT. "A-A"

FIG. 1




PACKAGING VIEW

FIG. 2

POLARIZATION OPTION LOCATION

INSERT PK-07-N INTO SPECIFIED
POSITION AND BREAK OFF TAB



NOTES:

- CONTACT PUSHOUT FORCE: .5 LB MIN.
- MAX ALLOWABLE CUT FLASH: .015 [.38] MAX.
- Δ REPRESENTS A CRITICAL DIMENSION.
- MATTE TIN PLATING DOES NOT ENABLE LEAD FREE SURFACE MOUNT PROCESSING

TABLE 2

ROW SPEC.	NO. OF POS.	PKG TUBE	TUBE PLUG
-D	05-50	PT-1-24-01-22	TP-03
-T	05-50	PT-1-24-06-15	TP-03
-Q	05-50	PT-1-24-15-29	TP-07
-D, -T & -Q	02-04	LAYER PACKAGING	

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING, RECORDING,
OR BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT
THE WRITTEN CONSENT OF SAMTEC INC.

EXISPROD\ASSEMBLY\2MM
SQW-ASM

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
BURRES 8-19-96

SQW-1XX-XX-XXX-X-XXX
SHEET 1 OF 1