

# 10/100 Base-X Module for Hex Port Applications

## EPF8147S


- Recommended for 10/100 Solution •
- Guaranteed to operate with 8 mA DC bias at 70°C •
- Complies with or exceeds IEEE 802.3, 10 BT/100 BX Standards •

### Electrical Parameters @ 25° C


| OCL<br>@ 70°C                     | Insertion Loss<br>(dB Max.) |     |            |     |            |     | Return Loss<br>(dB Min.) |     |           |     |            |     | Common Mode Rejection<br>(dB Min.) |     |            |     |            |     |            |     | Crosstalk<br>(dB Min.) |
|-----------------------------------|-----------------------------|-----|------------|-----|------------|-----|--------------------------|-----|-----------|-----|------------|-----|------------------------------------|-----|------------|-----|------------|-----|------------|-----|------------------------|
| 100 KHz, 0.1 Vrms<br>8 mA DC Bias | 1-80<br>MHz                 |     | 100<br>MHz |     | 150<br>MHz |     | 1-30<br>MHz              |     | 60<br>MHz |     | 100<br>MHz |     | 1-100<br>MHz                       |     | 200<br>MHz |     | 300<br>MHz |     | 500<br>MHz |     | 1-100<br>MHz           |
| Media Side                        | Xmit                        | Rcv | Xmit       | Rcv | Xmit       | Rcv | Xmit                     | Rcv | Xmit      | Rcv | Xmit       | Rcv | Xmit                               | Rcv | Xmit       | Rcv | Xmit       | Rcv | Xmit       | Rcv |                        |
| 350μH                             | -1                          | -1  | -1         | -1  | -3         | -3  | -18                      | -18 | -18       | -18 | -10        | -10 | -30                                | -20 | -25        | -15 | -20        | -10 | -15        | --- | -30                    |

• Isolation : 1500 Vrms • Impedance : 100 Ω • Rise Time : 3.0 nS Max. •

### Schematic



### Package



### Dimensions

| Dim. | (Inches) |      |      | (Millimeters) |       |       |
|------|----------|------|------|---------------|-------|-------|
|      | Min.     | Max. | Nom. | Min.          | Max.  | Nom.  |
| A    | 1.61     | 1.63 | 1.62 | 40.89         | 41.40 | 41.15 |
| B    | .470     | .490 | .480 | 11.94         | 12.45 | 12.19 |
| C    | .235     | .255 | .245 | 5.97          | 6.48  | 6.22  |
| D    | ---      | ---  | 1.45 | ---           | ---   | 36.83 |
| E    | .010     | .015 | .013 | .254          | .381  | .330  |
| F    | ---      | ---  | .050 | ---           | ---   | 1.27  |
| G    | .590     | .610 | .600 | 14.99         | 15.49 | 15.24 |
| H    | .018     | .022 | .020 | .457          | .559  | .508  |
| I    | .008     | .012 | .010 | .203          | .305  | .254  |
| J    | ---      | ---  | .085 | ---           | ---   | 2.16  |
| K    | 0°       | 8°   | ---  | 0°            | 8°    | ---   |
| L    | .025     | .045 | .035 | .635          | 1.14  | .889  |
| M    | ---      | ---  | .030 | ---           | ---   | .762  |
| N    | ---      | ---  | .050 | ---           | ---   | 1.27  |
| P    | ---      | ---  | .090 | ---           | ---   | 2.29  |
| Q    | ---      | ---  | .670 | ---           | ---   | 17.02 |