



PartNumber	127050-0204
Actuation	Manual
Current Rating	5 A max. per line
Number of Positions	156
Product Group	DLM
Actuating Camshaft Material	Stainless steel, Passivated
Shock	MIL-STD-202 Test Method 213, Condition A (50 G's)
Humidity	MIL-STD-202 Test Method 103, Condition B
Where Sold	Europe, Americas
Component	Connector
Insulator Retainer Material	Stainless steel, Passivated
Insulator Material	Glass filled thermoplastic, UL 94V-0 rated, Color: Black
Insulation Resistance	5000 M ohms min.
Polarization	Polarizing Posts
Footnote	Dimension are shown in mm (inch).
Housing	Metal
Wire Accomodation	#42 AWG to #18 AWG
Dielectric Withstanding Voltage	1200 V AC RMS
Termination Type	Wire Crimp (Contacts sold separately)
Housing Material	Aluminum alloy, nickel plated
Connector Durability	10,000 mating cycles min.
Salt Spray	MIL-STD-202 Test Method 101, Condition B (48 Hours)
Nomenclature	DLM1-156P
Gender	Plug
Crimp Contact Material	Copper alloy, 50μ inches gold over 50 μ inches nickel in mating area, gold flash on balance
Contact Resistance	15 m ohms max. (20 m ohms max. - #32 AWG - #30 AWG contact)
Contact Spacing	2,54 (.100) Square Grid
Contact Retention	8 lbs (35,585 N) min.
Operating Temperature	-55°C to 105°C
Vibration	MIL-STD-202 Test Method 204, Condition C





