

Technical specification:






Rated voltage:	3pos	4pos
IEC 61076-2-104	60 V	30 V
Current rating:	4 A at 40 °C with 0,5mm ²	
IEC 61076-2-104		
Insulation resistance:	>= 100 MΩ	
IEC 60512		
Pollution degree:	3/2	
IEC 60664-1		
Degree of protection:	IP 67, in mated condition	
IEC 60529		
Temperature range:	-30 °C ... +85 °C	
IEC 60664-1		
Mating cycles:	>= 100	
IEC 60512-9a		
Wire cross section:	AWG 20 / max. 0,5 mm ²	

Materials:

Contact:	CuZn
Contact plating:	Au over Ni in mating area
Contact carrier:	PA6, UL 94
Cable sealing:	NBR
O-Ring:	Silicone / NBR
Coupling nut:	CuZn, Ni
Housing:	PA6 GF, UL 94

Installation specification for locking nut to counter connector:

Recommended torque:	0,4 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220




Part no:	Description:	Pos:	Cable-Ø:
42-00010	SAL - 8 - RKC3-S	3	4 - 5,5mm
42-00012	SAL - 8 - RKC4-S	4	4 - 5,5mm

DO NOT ALTER CAD DRAWING BY HAND

Directive 2002/95/EC RoHS compliant

Indndex: c 18.07.13 KH Ä4842
Wire cross section adapted



dim. in mm

tolerance of cable:

general tolerance: 0 ± 0,50mm
0,0 ± 0,25mm
0,00 ± 0,10mm

CONEC®

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND
MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

title:

Female connector M8x1, field
attachable , axial, screw termination

dwg no:

42K1A316

part no:

see table