

AMPHENOL PART NUMBER CONFIGURATION

U90 - G 3X1 - 1XXX

HEAT SINK OPTION

- 1 = NO HEAT SINK OR CLIP SHIPPED
- 5 = PIN STYLE HEAT SINK AND CLIP (H1=15.1; H2=6.5; SAN HEIGHT)
- 6 = PIN STYLE HEAT SINK AND CLIP (H1=12.8; H2=4.2; PCI HEIGHT)
- 7 = PIN STYLE HEAT SINK AND CLIP (H1= 22.1; H2=13.5; TALL)
- D = PIN-FIN STYLE HEAT SINK AND CLIP (H1=15.1; H2=6.5; SAN HEIGHT)
- E = PIN-FIN STYLE HEAT SINK AND CLIP (H1=12.8; H2=4.2; PCI HEIGHT)
- F = PIN-FIN STYLE HEAT SINK AND CLIP (H1= 22.1; H2=13.5; TALL)
- K = PIN STYLE HEAT SINK AND CLIP (H1=18.1; H2=9.5; CUSTOM HEIGHT)

NOTE:
FOR LOCATION OF "H1" AND "H2" DIMENSIONS SEE SHEET 2

PACKAGING OPTIONS

- 0 = TRAY PACKAGING (HEAT SINK & CLIP SHIPPED IN SEPARATE TRAY, IF ORDERED)
- A = TRAY PACKAGING, HEAT SINK & CLIP SHIPPED ASSEMBLED
- B = TRAY PACKAGING, HEAT SINK & CLIP SHIPPED ASSEMBLED WITH LIGHT PIPE BULK PACKED

LIGHT PIPE AND BEHIND BEZEL COVER OPTIONS

- 0 = STANDARD (NO LIGHT PIPES)
- 1 = WITH ROUND LIGHT PIPES
- 2 = WITH ROUND LIGHT PIPES AND WITH BEHIND BEZEL EMI GASKET SHIPPED LOOSE
- 3 = WITH SQUARE LIGHT PIPES
- 7 = WITH ROUND SINGLE BARREL LIGHT PIPE
- B = WITH SQUARE LIGHT PIPES, WITH LIGHT INLET SURFACE AT 1.45 mm OFF THE PCB

OPTIONAL DUST COVER

- 0 = WITHOUT DUST COVER
- D = WITH DUST COVER (SHIPPED AS LOOSE PIECE)

REV - DESCRIPT - DATE - APPRVD


U - CORRECTED EMI GASKET NOTE --- SEP 29/10

V - CUTOUT POSITION REVISED --- JAN 03/12


W - ADDED NEW OPTION --- JUN 19/12

Z - ADDED NEW OPTION "B" --- SEP 10/12


Y - ADDED NEW OPTION "K" --- OCT 15/12



PART NUMBER SHOWN
U90-G351-101A




PART NUMBER SHOWN
U90-G351-107A



PART NUMBER SHOWN
U90-G3D1-101A

BEHIND BEZEL EMI
GASKET (OPTIONAL)
P/N: U90-1320-8010-BP

DUST COVER(OPTIONAL)
P/N: U90-1401-8000BP





PART NUMBER SHOWN
U90-G351-1D2A
(EXPLODED VIEW)


DO NOT SCALE DRAWING
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE
OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
DECIMALS	ANGLES	DRAWN	MAY 23/08			
.XX ± .10	± 1°	DESIGNED	MAY 23/08	QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK, CLIP AND LIGHT PIPE		
.X ± .25		CHECKED				
MATERIAL AND FINISH		QA APP'D		SIZE	DWG. NO.	REV.
REF.		IE APP'D		C	P-U90-G3X1-1XXX	Y
CODE IDENT. NO.		DWG APP'D	DEC.5.07	SCALE	PROJECT	SHEET
		A.GREEN		2:1	PROJECT	1 OF 11



PART NUMBER SHOWN
U90-G351-101A
(WITH ROUND LIGHT PIPE)




NOTES:



- MATERIAL:
CAGE AND EMI SPRINGS: COPPER ALLOY
FRONT FLANGE: ZINC DIE CAST
HEAT SINK CLIP: STEEL ALLOY
PIN-FIN STYLE HEAT SINK: ALUMINUM
PIN STYLE HEAT SINK: NICKEL PLATED ALUMINUM
CAGE PLATING: 3.81µm [100µ"] MIN. NICKEL.
LIGHT PIPE: GE LEXAN, OPTICAL GRADE
- CAGE IS INTENDED FOR USE WITH THE
QUAD SMALL FORM-FACTOR PLUGGABLE (QSFP)
TRANSCEIVER SPECIFICATION INF-8438i.

DIMENSION "H1" SHOWN IN UN-PLUGGED STATE		
PART NUMBER	DIM. "H1"	DIM. "H2"
U90-G351-1XXX	15.03	6.50
U90-G361-1XXX	12.37	4.20
U90-G371-1XXX	22.03	13.50
U90-G3D1-1XXX	15.03	6.50
U90-G3E1-1XXX	12.37	4.20
U90-G3F1-1XXX	22.03	13.50
U90-G3K1-1XXX	18.03	9.50





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE: DECIMALS ANGLES .XX ± .10 ± 1° .X ± .25 MATERIAL AND FINISH	APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
	DRAWN Z.LJ	MAY 23/08			
	DESIGNED ZLJ	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK, CLIP AND LIGHT PIPE		
	CHECKED				
REF.	QA APP'D		SIZE C	DWG. NO. P-U90-G3X1-1XXX	REV. Y
	IE APP'D		SCALE 2:1	PROJECT PROJECT	SHEET 2 OF 11
CODE IDENT. NO.	DWG APP'D A.GREEN	DEC.5,07			





PART NUMBER SHOWN
U90-G351-103A
(WITH SQUARE LIGHT PIPE)





NOTES:

- MATERIAL:
CAGE AND EMI SPRINGS: COPPER ALLOY
FRONT FLANGE: ZINC DIE CAST
HEAT SINK CLIP: STEEL ALLOY
PIN-FIN STYLE HEAT SINK: ALUMINUM
PIN STYLE HEAT SINK: NICKEL PLATED ALUMINUM
CAGE PLATING: 3.81µm [100µ"] MIN. NICKEL.
LIGHT PIPE: GE LEXAN, OPTICAL GRADE
- CAGE IS INTENDED FOR USE WITH THE
QUAD SMALL FORM-FACTOR PLUGGABLE (QSFP)
TRANSCEIVER SPECIFICATION INF-8438i.


DIMENSION "H1" SHOWN IN UN-PLUGGED STATE		
PART NUMBER	DIM. "H1"	DIM. "H2"
U90-G351-1XXX	15.03	6.50
U90-G361-1XXX	12.37	4.20
U90-G371-1XXX	22.03	13.50
U90-G3D1-1XXX	15.03	6.50
U90-G3E1-1XXX	12.37	4.20
U90-G3F1-1XXX	22.03	13.50
U90-G3K1-1XXX	18.03	9.50




UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
DECIMALS	ANGLES	DRAWN	MAY 23/08			
.XX ±.10	± 1°	DESIGNED	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK, CLIP AND LIGHT PIPE		
.X ±.25		CHECKED				
MATERIAL AND FINISH		QA APP'D		SIZE	DWG. NO.	REV.
		IE APP'D		C	P-U90-G3X1-1XXX	Y
REF.		DWG APP'D		SCALE	PROJECT	SHEET
CODE IDENT. NO.		A.GREEN	DEC.5,07	2:1	PROJECT	3 OF 11



PART NUMBER SHOWN
U90-G351-107A
(WITH SINGLE BARREL
ROUND LIGHT PIPE)



SECTION BG-BG
SCALE 2.5 : 1



SECTION BH-BH
SCALE 2.5 : 1


NOTES:


- MATERIAL:
CAGE AND EMI SPRINGS: COPPER ALLOY
FRONT FLANGE: ZINC DIE CAST
HEAT SINK CLIP: STEEL ALLOY
PIN-FIN STYLE HEAT SINK: ALUMINUM
PIN STYLE HEAT SINK: NICKEL PLATED ALUMINUM
CAGE PLATING: 3.81µm [100µ"] MIN. NICKEL.
LIGHT PIPE: GE LEXAN, OPTICAL GRADE
- CAGE IS INTENDED FOR USE WITH THE
QUAD SMALL FORM-FACTOR PLUGGABLE (QSFP)
TRANSCEIVER SPECIFICATION INF-8438i.

DIMENSION "H1" SHOWN IN UN-PLUGGED STATE		
PART NUMBER	DIM. "H1"	DIM. "H2"
U90-G351-1XXX	15.03	6.50
U90-G361-1XXX	12.37	4.20
U90-G371-1XXX	22.03	13.50
U90-G3D1-1XXX	15.03	6.50
U90-G3E1-1XXX	12.37	4.20
U90-G3F1-1XXX	22.03	13.50
U90-G3K1-1XXX	18.03	9.50



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
		DRAWN Z.LJ	MAY 23/08			
DECIMALS ANGLES .XX ± .10 ± 1° .X ± .25		DESIGNED ZLJ	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK,CLIP AND LIGHT PIPE		
MATERIAL AND FINISH		CHECKED				
		QA APP'D				
		IE APP'D				
REF.		DWG APP'D A.GREEN	DEC.5,07	SIZE C	DWG. NO. P-U90-G3X1-1XXX	REV. Y
CODE IDENT. NO.				SCALE 2:1	PROJECT PROJECT	SHEET 4 OF 11






RECOMMENDED HOST PCB BOARD
BEHIND BEZEL BELLY TO BELLY LAYOUT
FOR DOUBLE BARREL LIGHT PIPE
(COMPONENT SIDE OF BOARD)

NOTES:

1. DATUM X AND Y ESTABLISHED BY CUSTOMER'S FUDUCIAL.
2. LOCATION OF EDGE OF PCB IS APPLICATION SPECIFIC.
3. FINISHED HOLE SIZE.




DETAIL C
SCALE 4 : 1


3.20±0.32
FOR BELLY TO BELLY APPLICATION



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
DECIMALS ANGLES .XX ± .10 ± 1° .X ± .25		DRAWN Z.LJ	MAY 23/08			
MATERIAL AND FINISH		DESIGNED ZLJ	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK,CLIP AND LIGHT PIPE		
		CHECKED				
		QA APP'D				
REF.		IE APP'D		SIZE C	DWG. NO. P-U90-G3X1-1XXX	REV. Y
CODE IDENT. NO.		DWG APP'D A.GREEN	DEC.5/07	SCALE 5:2	PROJECT PROJECT	SHEET 5 OF 11



**RECOMMENDED HOST PCB BOARD
SINGLE LEVEL MOUNTING LAYOUT
FOR DOUBLE BARREL LIGHT PIPE
(COMPONENT SIDE OF BOARD)**





NOTES:

- DATUM X AND Y ESTABLISHED BY CUSTOMER'S FUDUCIAL.
- LOCATION OF EDGE OF PCB IS APPLICATION SPECIFIC.
- FINISHED HOLE SIZE.

DO NOT SCALE DRAWING
THIS DOCUMENT COTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com	
DECIMALS	ANGLES	DRAWN Z.LJ	MAY 23/08		
.XX $\pm .10$	$\pm 1^\circ$	DESIGNED ZLJ	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK, CLIP AND LIGHT PIPE	
.X $\pm .25$		CHECKED			
MATERIAL AND FINISH		QA APP'D		SIZE C	DWG. NO. P-U90-G3X1-1XXX
REF.		IE APP'D		SCALE 2:1	PROJECT PROJECT
CODE IDENT. NO.		DWG APP'D A.GREEN	DEC.5/07	SHEET 6 OF 11	




**RECOMMENDED HOST PCB BOARD
SINGLE LEVEL MOUNTING LAYOUT
FOR SINGLE BARREL LIGHT PIPE
(COMPONENT SIDE OF BOARD)**

- NOTES:
- DATUM X AND Y ESTABLISHED BY CUSTOMER'S FUDUCIAL.
 - LOCATION OF EDGE OF PCB IS APPLICATION SPECIFIC.
 - FINISHED HOLE SIZE.




UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
DECIMALS	ANGLES	DRAWN Z.LJ	MAY 23/08			
.XX ±.10	±1°	DESIGNED ZLJ	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK, CLIP AND LIGHT PIPE		
.X ±.25		CHECKED				
MATERIAL AND FINISH		QA APP'D		SIZE C	DWG. NO. P-U90-G3X1-1XXX	REV. Y
REF.		IE APP'D		SCALE 2:1	PROJECT PROJECT	SHEET 7 OF 11
CODE IDENT. NO.		DWG APP'D A.GREEN	DEC.5/07			



RECOMMENDED HOST PCB BOARD
BEHIND BEZEL BELLY TO BELLY LAYOUT
FOR SINGLE BARREL LIGHT PIPE
(COMPONENT SIDE OF BOARD)

NOTES:

1. DATUM X AND Y ESTABLISHED BY CUSTOMER'S FUDUCIAL.
2. LOCATION OF EDGE OF PCB IS APPLICATION SPECIFIC.
3. FINISHED HOLE SIZE.





DETAIL BM
SCALE 4 : 1

3.20±0.32
FOR BELLY TO BELLY APPLICATION





UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
DECIMALS ANGLES .XX ± .10 ± 1° .X ± .25		DRAWN Z.LJ	MAY 23/08			
MATERIAL AND FINISH		DESIGNED ZLJ	MAY 23/08	QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK,CLIP AND LIGHT PIPE		
		CHECKED				
		QA APP'D				
REF.		IE APP'D		SIZE C	DWG. NO. P-U90-G3X1-1XXX	REV. Y
CODE IDENT. NO.		DWG APP'D A.GREEN	DEC.5/07	SCALE 5:2	PROJECT PROJECT	SHEET 8 OF 11




7	SCALE 1:1	PROJECT PROJECT	SHEET 9 OF 11
---	--------------	--------------------	------------------

DO NOT SCALE DRAWING






U90-G3X1-1X 3 X	2.20
U90-G3X1-1X B X	1.45



CODE IDENT. NO.

A.GREEN

DEC.5,07



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenol-highspeed.com		
DECIMALS ANGLES .XX ± .10 ± 1° .X ± .25		DRAWN Z.LJ	MAY 23/08			
MATERIAL AND FINISH		DESIGNED ZLJ	MAY 23/08	TITLE QSFP 1x3 CAGE BEHIND BEZEL WITH HEATSINK,CLIP AND LIGHT PIPE		
		CHECKED				
		QA APP'D				
REF.		IE APP'D		SIZE C	DWG. NO. P-U90-G3X1-1XXX	REV. Y
CODE IDENT. NO.		DWG APP'D A.GREEN	DEC.5,07	SCALE 1:1	PROJECT PROJECT	SHEET 11 OF 11

DO NOT SCALE DRAWING
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE
OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.