

MIN. CAP. (μF)		WORKING VOLTAGE DC		CURRENT D.C.	I.R. MIN.	D.W.V.	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220						TEMPERATURE CHARACTERISTIC
		85°C	125°C				30 KHz	100 KHz	300 KHz	1 MHz	10 MHz	1 GHz	
1.4		100	70	15 A	500 M Ω	125 VDC	15	25	34	44	60	70	X7W

REVISION RECORD

Original Release	C.O.	20020607-3-01
WORKING VOLTAGE REV'D 100, 70 WERE 80, 50 & TEMP. CHARAC. ADDED	1	20020903-1-03
ADDED AND REVISED NOTES. S.M. 01-25-06	2	20060123-2-02

--TOLERANCES-- Unless Otherwise Specified	COAXIAL BROADBAND - "L" HERMETICALLY SEALED	
DECIMAL ±		
ANGLES ±		
 TUCSON, ARIZONA	Title S.M. 06-10-02	Drawn S.M. 06-10-02
	Approved B.Mc 06-10-02	Scale x 3

AZ-0115 REV'D

A

4601-052