



Solving your relay requirements since 1922

Amperite Co.

(800) 752-2329

www.Amperite.com

ST1A Series Solid State Delay-On-Make Timers



... 100% solid state circuitry - no moving parts

... CMOS digital timing circuitry


... Fixed or field adjustable delays from milliseconds to hours

... 2 amperes continuous load current (10 amperes available, consult factory)

Timing Mode:

Delay on operate begins upon application of input power. The load is energized at the end of the delay period and remains so until input power is removed.

Timing Diagram:



Contact Information:

Solid state switching device 1 form A; normally open series connection. Continuous current rating 2 amperes. Maximum inrush 20 amperes. Voltage drop 2.5 volts RMS or less @ 2 amperes. (For 10 ampere load current rating consult factory).

Note: Maximum current rating for 110V DC is 2 amperes (heat sink required).

)

Timing Specifications:

Timing: Factory fixed, or 0.1 seconds to 100 hours in any of the ranges below. Timing is set by user supplied resistor or potentiometer. Custom timing available.

Timing ranges:


.1 to 10 seconds	1 to 100 minutes
.2 to 20 seconds	10 to 1000 minutes
1 to 100 seconds	.1 to 10 hours
10 to 1000 seconds	1 to 100 hours
.1 to 10 minutes	

Timing tolerance: fixed units +/- 10%

Timing repeatability: 2%

Timing cycle interrupt transfer: none

Outline Dimensions:



AC (60 Hz) and DC Input Voltages & Limits

Nominal	Minimum	Maximum
12V	10V	14V
24V	20V	28V
48V	41V	55V



Solving your relay requirements since 1922


Amperite Co.

(800) 752-2329



www.Amperite.com

110V	95V	125V
120V	105V	130V
230V	190V	255V

External Resistor Selection:



Wiring Diagrams:



Mechanical Information:

Enclosure 2 X 2 X 3/4 inch black plastic, epoxy sealed. Center hole mounting. Three or five 1/4 inch quick connect male terminals

 AMPERITE® Solving your relay requirements since 1922	Amperite Co. (800) 752-2329 www.Amperite.com
--	--



Ordering Information:

Definition of a part number for the Amperite ST1A Series Time Delay Relay:

Example:

120 A .1 - 10 M ST1A
 ↑ ↑ ↑ ↑ ↑ ↑
 A B C D E F

A: Denotes nominal input voltage. Voltages available: 12V, 24V, 120V & 230V AC; 12V, 24V, 48V & 110V DC. **Custom voltages are available.**

B: Denotes type of input power required for operation: A = AC - Alternating Current; D = DC - Direct Current.

C & D: Denotes range of adjustability by using an external resistor or potentiometer, where C is the minimum timing and D is the maximum timing. Standard timing span is 100:1. For fixed timing units specify a single number.

E: Denotes unit of time delay: S=seconds; M=minutes; H=hours.

F: Denotes Amperite ST1A Series solid state, delay-on-make timer.



Solving Your Relay Requirements Since 1922