



DO-214AA
(SMB J-Bend)

$V_{(BR)}$ Unidirectional
6.8 to 540V
 $V_{(BR)}$ Bidirectional
6.8 to 220V
Peak Pulse Power 600W

Mounting Pad Layout



Mechanical Data

Case: JEDEC DO-214AA (SMB) molded plastic over passivated junction

Terminals: Solder plated, solderable per MIL-STD-750, Method 2026. High temperature soldering guaranteed: 250°C/10 seconds at terminals.

Polarity: For uni-directional types the band denotes the cathode, which is positive with respect to the anode under normal TVS operation.

Standard Packaging: 12mm tape (EIA STD RS-481)

Weight: 0.003oz., 0.093g

Packaging Codes – Options (Antistatic):

51 – 2K per Bulk box, 20K/carton

52 – 750 per 7" plastic Reel (12mm tape), 15K/carton

5B – 3.2K per 13" plastic Reel (12mm tape), 32K/carton

Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- Low profile package with built-in strain relief for surface mounted applications
- Glass passivated junction
- Low incremental surge resistance
- 600W peak pulse power capability with a 10/1000 μ s waveform, repetition rate (duty cycle): 0.01%
- Excellent clamping capability
- Very fast response time

*Voltages above 220V available Q3-2002

Devices for Bidirectional Applications

For bi-directional devices, use suffix CA (e.g. P6SMB10CA). Electrical characteristics apply in both directions.

Maximum Ratings & Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	Value	Unit
Peak power dissipation with a 10/1000 μ s waveform ⁽¹⁾⁽²⁾ (Fig. 1)	PPPM	Minimum 600	W
Peak pulse current with a 10/1000 μ s waveform ⁽¹⁾	IPPM	See Next Table	A
Power dissipation on infinite heatsink, $T_A = 50^\circ\text{C}$	PM(AV)	5.0	W
Peak forward surge current 8.3ms single half sine-wave uni-directional only ⁽²⁾	IFSM	100	A
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +150	°C
Thermal resistance junction to ambient air ⁽³⁾	$R_{\theta JA}$	100	°C/W
Thermal resistance junction to leads	$R_{\theta JL}$	20	°C/W
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +150	°C

Notes: (1) Non-repetitive current pulse, per Fig.3 and derated above $T_A = 25^\circ\text{C}$ per Fig. 2.

(2) Mounted on 0.2 x 0.2" (5.0 x 5.0mm) copper pads to each terminal

(3) Mounted on minimum recommended pad layout

Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. $V_F = 3.5V$ at $I_F = 50A$ (uni-directional only)

General Semiconductor Part Number	Device Marking Code		Breakdown Voltage $V_{(BR)}$ at $I_T^{(1)}$ (V)		Test Current I_T (mA)	Stand-off Voltage V_{WM} (V)	Maximum Reverse Leakage at V_{WM} $I_D^{(3)}$ (μA)	Maximum Peak Pulse Current $I_{PPM}^{(2)}$ (A)	Maximum Clamping Voltage at I_{PPM} V_C (V)	Maximum Temp. Coefficient of $V_{(BR)}$ ($\%/^{\circ}C$)
	UNI	BI	Min	Max						
P6SMB6.8A	6V8A	6V8C	6.45	7.14	10	5.80	1000	57.1	10.5	0.057
P6SMB7.5A	7V5A	7V5C	7.13	7.88	10	6.40	500	53.1	11.3	0.061
P6SMB8.2A	8V2A	8V2C	7.79	8.61	10	7.02	200	49.6	12.1	0.065
P6SMB9.1A	9V1A	9V1C	8.65	9.55	1.0	7.78	50	44.8	13.4	0.068
P6SMB10A	10A	10C	9.50	10.5	1.0	8.55	10	41.4	14.5	0.073
P6SMB11A	11A	11C	10.5	11.6	1.0	9.40	5.0	38.5	15.6	0.075
P6SMB12A	12A	12C	11.4	12.6	1.0	10.2	5.0	35.9	16.7	0.078
P6SMB13A	13A	13C	12.4	13.7	1.0	11.1	5.0	33.0	18.2	0.081
P6SMB15A	15A	15C	14.3	15.8	1.0	12.8	1.0	28.3	21.2	0.084
P6SMB16A	16A	16C	15.2	16.8	1.0	13.6	1.0	26.7	22.5	0.086
P6SMB18A	18A	18C	17.1	18.9	1.0	15.3	1.0	23.8	25.2	0.088
P6SMB20A	20A	20C	19.0	21.0	1.0	17.1	1.0	21.7	27.7	0.090
P6SMB22A	22A	22C	20.9	23.1	1.0	18.8	1.0	19.6	30.6	0.092
P6SMB24A	24A	24C	22.8	25.2	1.0	20.5	1.0	18.1	33.2	0.094
P6SMB27A	27A	27C	25.7	28.4	1.0	23.1	1.0	16.0	37.5	0.096
P6SMB30A	30A	30C	28.5	31.5	1.0	25.6	1.0	14.5	41.4	0.097
P6SMB33A	33A	33C	31.4	34.7	1.0	28.2	1.0	13.1	45.7	0.098
P6SMB36A	36A	36C	34.2	37.8	1.0	30.8	1.0	12.0	49.9	0.099
P6SMB39A	39A	39C	37.1	41.0	1.0	33.3	1.0	11.1	53.9	0.100
P6SMB43A	43A	43C	40.9	45.2	1.0	36.8	1.0	10.1	59.3	0.101
P6SMB47A	47A	47C	44.7	49.4	1.0	40.2	1.0	9.3	64.8	0.101
P6SMB51A	51A	51C	48.5	53.6	1.0	43.6	1.0	8.6	70.1	0.102
P6SMB56A	56A	56C	53.2	58.8	1.0	47.8	1.0	7.8	77.0	0.103
P6SMB62A	62A	62C	58.9	65.1	1.0	53.0	1.0	7.1	85.0	0.104
P6SMB68A	68A	68C	64.6	71.4	1.0	58.1	1.0	6.5	92.0	0.104
P6SMB75A	75A	75C	71.3	78.8	1.0	64.1	1.0	5.8	103	0.105
P6SMB82A	82A	82C	77.9	86.1	1.0	70.1	1.0	5.3	113	0.105
P6SMB91A	91A	91C	86.5	95.5	1.0	77.8	1.0	4.8	125	0.106
P6SMB100A	100A	100C	95.0	105	1.0	85.5	1.0	4.4	137	0.106
P6SMB110A	110A	110C	105	116	1.0	94.0	1.0	3.9	152	0.107
P6SMB120A	120A	120C	114	126	1.0	102	1.0	3.6	165	0.107
P6SMB130A	130A	130C	124	137	1.0	111	1.0	3.4	179	0.107
P6SMB150A	150A	150C	143	158	1.0	128	1.0	2.9	207	0.108
P6SMB160A	160A	160C	152	168	1.0	136	1.0	2.7	219	0.108
P6SMB170A	170A	170C	162	179	1.0	145	1.0	2.6	234	0.108
P6SMB180A	180A	180C	171	189	1.0	154	1.0	2.4	246	0.108
P6SMB200A	200A	200C	190	210	1.0	171	1.0	2.2	274	0.108
P6SMB220A	220A	220C	209	231	1.0	185	1.0	1.8	328	0.108
P6SMB250A	250A	—	237	263	1.0	214	1.0	1.74	344	0.110
P6SMB300A	300A	—	285	315	1.0	256	1.0	1.45	414	0.110
P6SMB350A	350A	—	333	368	1.0	300	1.0	1.24	482	0.110
P6SMB400A	400A	—	380	420	1.0	342	1.0	1.10	548	0.110
P6SMB440A	440A	—	418	462	1.0	376	1.0	1.00	602	0.110
P6SMB480A	480A	—	456	504	1.0	408	1.0	0.91	658	0.110
P6SMB510A	510A	—	485	535	1.0	434	1.0	0.86	698	0.110
P6SMB540A	540A	—	513	567	1.0	459	1.0	0.81	740	0.110

- Notes:** (1) Pulse test: $t_p \leq 50ms$
(2) Surge current waveform per Fig. 3 and derate per Fig. 2
(3) For bidirectional types with V_{WM} of 10 volts and less, the I_D limit is doubled
(4) All terms and symbols are consistent with ANSI/IEEE C62.35

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig. 1 – Peak Pulse Power Rating Curve




Fig. 2 – Pulse Derating Curve




Fig. 3 – Pulse Waveform




Fig. 4 – Typical Junction Capacitance




Fig. 5 – Typical Transient Thermal Impedance




Fig. 6 – Maximum Non-Repetitive Peak Forward Surge Current

