

Single-Phase Metered PDU, 1.4kW 15A 120V, 1U Horizontal Rackmount, 13 NEMA 5-15R outlets, NEMA 5-15P input, 15ft / 4.5m cord

MODEL NUMBER: PDUMH15



Description

Tripp Lite Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital meter. Enables visual current monitoring of PDU output current to prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA 5-15P 15A 120V input plug with 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

Specifications

OVERVIEW	
PDU Type	Metered
OUTPUT	

Highlights

- Metered single phase 15A 120V PDU
- 1U horizontal rackmount; digital current meter
- NEMA 5-15P input; 15 ft. / 4.5m line cord
- 13 NEMA 5-15R outlets (1 front / 12 rear)
- Reversible housing; 4.5 in. / 11.4 cm depth

Applications

- Multi-outlet power distribution unit with digital current monitoring is the ideal means of powering multiple loads in 19 inch rackmount, wall-mount, and under-counter applications such as internetworking, PC systems, telecommunications, audio visual, security, sound reinforcement, and more. Ideal distribution of alternate and sinewave UPS and generator power or commercially derived AC power to connected equipment.

Package Includes

- PDUMH15 Metered rackmount PDU
- Owner's manual with warranty information

Output Capacity Details 1.4kW (120V input), 1.5kW (127V input), 1.2kW (100V input); 15A maximum (Agency de-rated to 12A continuous)	
Frequency compatibility	50 / 60 Hz
Output nominal voltage	100-127V nominal, single phase
Overload protection	15
Outlet quantity / type	13 NEMA 5-15R
Outlet Type	NEMA 5-15R
INPUT	
PDU Input Voltage	100; 120; 127
Maximum Input Amps (A)	15
Maximum Input Amps (A) Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.57
Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Front panel LEDs	Digital LED current monitor display
PHYSICAL	
Shipping Dimensions (HWD/in)	2.25 x 20.5 x 10
Shipping Dimensions (HWD/cm)	5.72 x 52.07 x 25.4
Shipping weight (lbs)	5.2
Shipping weight (kg)	2.36
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 4.5
Unit Dimensions (HWD/cm)	4.45 x 44.45 x 11.43
Unit weight (lbs)	4.5
Unit weight (kg)	2.04
Material of construction	Sheet Metal
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form factors supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets center to center measurement	Rear Side = 30.20mm
SPECIAL FEATURES	
Appearance	All black color scheme

TVSS grounding	Rear grounding lug
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

Related Items

Optional Products

Model Number	Description	Qty.
PDUINSIDE	Enables Vertical Installation of Select 1U PDUs, Power Strips and Surge Suppressors in SmartRack Configurations	1
P006-006-13LA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Left Angle)	1
P006-006-13RA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Right Angle)	1
P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P030-002-5	5-Pack of 2-ft. 18AWG Power Cords NEMA 5-15P to IEC-320-C13)	1
P006-003	3-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-004	4-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-004-BL	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Blue Connectors	1
P006-004-GN	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Green Connectors	1
P006-004-RD	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Red Connectors	1
P006-004-YW	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Yellow Connectors	1
P006-006	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-006-2	6-ft. AC Power Splitter Cable (NEMA 5-15P to 2 x IEC-320-C13)	1
P006-006-515MF	6 ft. Piggyback Power Cord (NEMA 5-15P/R to IEC-320-C13)	1
P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
P006-010	10-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/PDUMH15>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[PDUMH15](#)