

NZ2520S Series

■ Model name

NZ2520SB Frequency stability of $\pm 50 \times 10^{-6}$.

■ Application

- For compact mobile information equipment, such as DVC, DSC, notebook PC, and PDA



Pb
Free

RoHS Compliant
Directive 2002/95/EC

■ Features

- Compact and light. Dimensions and weight: 2.5 x 2.0 mm, 0.9 mm, and 0.02 g.
- This crystal clock oscillator can support low frequencies (from 1.5 MHz); an achievement not easy for other crystal oscillators of the same size to equal.
- Automatic mounting by taping and IR reflow (lead-free) are possible.
- Lead-free.

Absolute maximum rating
Power supply voltage (V_{DD}) –0.5 to +4.0 V
Storage temperature range –55 to +125 °C

■ Specifications

Item		Model								
Output level		C-MOS								
Frequency range ¹ (MHz)		1.5 ≤ F < 10 10 ≤ F < 20 20 ≤ F < 30 30 ≤ F < 40 40 ≤ F < 50 50 ≤ F < 60 60 ≤ F < 70 70 ≤ F < 80								
Operating temperature range ² (°C)		–40 to +85								
Frequency Stability ($\times 10^{-6}$)		±50								
Current consumption max	During operation	+3.3 V, 25 °C (mA)	3.5	4.5	5.0	5.5	6.0	7.0	8.0	9.0
	During standby	+3.3 V, 25 °C (μ A)	10							
V_{OL} max/ V_{OH} min (V)		0.1 V_{DD} /0.9 V_{DD}								
T_r max/ T_f max (ns)		5/5								
Duty Cycle min. to max. (%)		45 to 55								
Load (C _L) max (pF)		15								
Oscillation start time max (ms)		4								
Standby function		Available (tristate)								

*1: If you require a product with a frequency not given above, please contact us.


*2: If you require a product with an operating temperature range not given above, please contact us.

■ List of Codes for Placing an Order


List of Codes for Placing an Order	NSA3415E
Power supply voltage [V_{DD}] (V)	+3.3±0.33

NZ2520S Series

■ Dimensions



■ Output Waveform <C-MOS>



■ Standby Function

#1 Input	#3 Output
Level H ($0.7 V_{DD} \leq V_{IH} \leq V_{DD}$) or OPEN is selected.	Oscillation output ON
Level L ($V_{IL} \leq 0.3 V_{DD}$) is selected.	High impedance

■ How to Specify an Order

When ordering our products, specify them with an "Ordering Code" that consists of the following:

Model name – Frequency (up to 9 digits) M – Number for specifying an order

Example : When ordering a product with model name: NZ2520SB, frequency: 20 MHz, frequency stability: $\pm 50 \times 10^{-6}$, and power supply voltage: 3.3 V

Ordering Code: NZ2520SB – 20.000000M – NSA3415E

If you have any queries concerning our standard frequencies and numbers for specifying orders, please contact our sales representatives or visit our homepage (<http://www.ndk.com/>).