

FED MFG CODE 91929

CATALOG LISTING

1HM61

SWITCH-BASIC

X41914-HMM

REPLACES

PR-671

RELEASE NO.

CHECK

CHECK

7 MAY 69

CHECK DC 5

MAY 69

M B

1HM61



**DRAWING
NUMBER**

IX

✕

UN

51

Ab

24

B	C
	D

100

17 D
M

1

--	--

1

--	--


1

1	2
---	---

[illegible]

--	--

T



NOTE —

- ⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- 2 - FOR USE IN TEMPERATURE RANGE -300°F TO + 250°F
 - 3 - HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
 - 4 - ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
 - 5 - TERMINALS ARE TINNED FOR SOLDERING
 - 6 - DO NOT APPLY MORE THAN 1 1/2 INCH-POUNDS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS		ELECTRICAL DATA			SCALE 2 TO 1	
OPERATING FORCE — — — — 7 OZ MAX		CONTACT ARRANGEMENT S P D T			DO NOT SCALE PRINT	
RELEASE FORCE — — — — 1 OZ MIN		LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	UNLESS OTHERWISE NOTED	
DIFFERENTIAL TRAVEL — — — .006 MAX		28 VDC	2 AMP	4 AMP	DIMENSIONS ARE IN INCHES	
OVERTRAVEL — — — — .006 MIN		115 VAC (400 CYCLE)	2 AMP	2 AMP	TOLERANCES ARE: ONE PLACE () ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ±	
					WEIGHT .014 LB MAX	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1HM61](#)