







- 1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 DRAIN HOLES LOCATED AS SHOWN. OPTIONAL CONSTRUCTION - ALL DRAIN HOLES LOCATED 90° AS SHOWN IN DETAIL A.
- 6 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 7 SUPERSEDED BY 350833-4




3-DIMENSIONAL MODEL NTS



DETAIL A
OPTIONAL CONSTRUCTION



RECOMMENDED MOUNTING HOLE PATTERN
FOR 3.18 [.125] THICK P.C. BOARD

PHOSPHOR BRONZE, GOLD		2	NYLON,UL94V-0,WHITE		350833-4	
PHOSPHOR BRONZE, GOLD			NYLON,UL94V-0,WHITE		350833-2	
PHOSPHOR BRONZE, PRE-TIN		2	NYLON,UL94V-0,WHITE		350833-1	
CONTACT MATERIAL AND FINISH			HOUSING MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. LEWIS CHK R. SWING AP'D M. TRULL 10-02-98 10-02-98 10-02-98		TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± -		PRODUCT SPEC		
		1 PLC ± -		—		
		2 PLC ± 0.13 [.005]		—		
		3 PLC ± -		APPLICATION SPEC		
4 PLC ± -		ANGLES ± 0 ± 30°		—		
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A1		RESTRICTED TO —
				CAGE CODE 00779		DRAWING NO C-350833
				WEIGHT —		SCALE 5:1
				SHEET 1		OF 1
				REV N1		