



## FEATURES:

- ✓ The molded strain relief is directly bonded to the cable jacket for superior strength and durability.
- ✓ Teflon insulation and nickel tarnish resistant outer shells used in the BNC connector provide long life and reliability.
- ✓ Gold plated center contacts assure the most noise free connection possible.
- ✓ The connectors and cable are impedance matched.

## CABLE DESIGNATION & TYPE:

- 2249-C:** RG58C/U, 50 ohm cable makes it ideal for most test and measurement applications, RF transmission systems and Thinnet LAN applications.
- 2249-E:** RG59B/U, 75 ohm cable assembly for use with broadcast, video, and other signal applications.
- 2249-K:** RG174/U, smaller diameter 50 ohm cable for greater flexibility in tight applications. It is best suited for use in low power situations where small size and flexibility is important.
- 2249-M:** RG62A/U, 93 ohm cable, use when higher impedance, > 75 ohms is required.
- 2249-Y:** RG223/U, double shielded 50 ohm cable assembly for superior interference rejection.

## RATINGS:

Cable Designation	Type	Impedance ohms	Capacitance per 1 foot / 0,304 meters	Power Loss /100 Ft @ 1 MHz	Insulation	AWG	Center Strands X AWG	Wire Type	Jacket Material	Cable OD	Shield	Temperature (w/o connectors) °C
C	RG58C/U	50	30.8 pf	0.44 dB	PE	20	19X36	TC	PVCNC	.195	TCB	-40 to +85
E	RG59B/U	75	22.5 pf	0.60 dB	PE	23	Solid	BCCS	PVCNC	.242	BCB	-40 to +60
K	RG174/U	50	30.8 pf	1.90 dB	PE	26	7X34	BCCS	PVC	.110	TCB	-40 to +75
M	RG62A/U	93	13.5 pf	0.25 dB	SSPE	22	Solid	BCCS	PVCNC	.242	BCB / BCB	0 to +75
Y	RG223/U	50	30.8 pf	0.35 dB	PE	19	Solid	SPC	PVCNC	.212	SCB / SCB	-40 to +60

AWG = American Wire Gauge  
BCB = Bare Copper Braid  
BCCS = Bare Copper Covered Steel  
PE = Polyethylene  
PVC = Polyvinyl Chloride  
PVCNC = Polyvinyl Chloride Non-Contaminating

SCB = Silver Coated Braid  
SPC = Silver Plated Copper  
SSPE = Semi-Solid Polyethylene  
TC = Tinned Copper  
TCB = Tinned Copper Braid

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02"$  (.51 mm), .xxx =  $\pm .005"$  (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)  
For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)



**Model 2249  
Cable Assembly with BNC  
Male on Each End**



Voltage: 500 Vrms max from center conductor to shield and 33 Vac / 70 Vdc max from shield to earth in controlled hands free testing environments. *For CE compliance:* not intended for hand-held use at voltage above 33 Vrms / 70 Vdc.

**MATERIALS:**

*BNC Male:*

Body: Brass, Tarnish Resistant Nickel Plating

Dielectric: PTFE

Center Contact: Gold Plated Brass

*Strain Relief:*

PVC molded directly to cable and connectors

**ORDERING INFORMATION: Model 2249-type-length\***

Cable Type: C, E, K, M, Y. (see table for detail).

Cable Length\*: 6" (15,24cm), 12" (30,5cm), 24" (61,0cm), 36" (91,4cm), 48" (121,9cm), 60" (152,4cm), 72" (182,9cm), 96" (243,84cm), 120" (304,8cm), 144" (365,76cm), 180" (457,2cm), 240" (6096cm), 300" (762cm), 360" (914,4cm), 600" (1524cm).

Ordering Example: 2249-C-72 (type "C" cable with a 72" (182,9cm) length)

\* Custom lengths are available, contact Pomona Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02"$  (.51 mm), .xxx =  $\pm .005"$  (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)  
For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Pomona:

[2249-M-360](#) [2249-M-300](#) [2249-K-144](#) [2249-Y-6](#) [2249-M-72](#) [2249-M-48](#) [2249-M-36](#) [2249-M-12](#) [2249-M-96](#) [2249-Y-300](#) [2249-Y-96](#) [2249-K-96](#) [2249-M-6](#) [2249-M-240](#) [2249-K-600](#) [2249-Y-360](#) [2249-M-180](#) [2249-M-144](#) [2249-Y-600](#) [2249-M-24](#) [2249-M-60](#) [2249-M-600](#) [2249-E-96#](#)