



# Intel® Xeon® Processor E5-2418L (10M, 2.0 GHz, 6.4 GT/s Intel® QPI)

## Specifications

### Essentials

### Performance

### Memory Specifications

### Expansion Options

### Package Specifications

### Advanced Technologies

### Intel® Data Protection Technology

### Intel® Platform Protection Technology

## Compatible Products

## Product Images

## Ordering / sSpecs / Steppings

## Specifications

### Essentials

Status	Launched
Launch Date	Q2'12
Processor Number	E5-2418L
Intel® Smart Cache	10 MB
Intel® QPI Speed	6.4 GT/s
# of QPI Links	1
Embedded Options Available	 Yes
Lithography	32 nm
Recommended Customer Price	TRAY: \$454.00
Datasheet	<a href="#">Link</a>

### Performance

# of Cores	4
# of Threads	8
Processor Base Frequency	2 GHz
Max Turbo Frequency	2.1 GHz
TDP	50 W

### Memory Specifications

Max Memory Size (dependent on memory type)	384 GB
Memory Types	DDR3 800/1066/1333
Max # of Memory Channels	3
ECC Memory Supported *	 Yes

### Expansion Options

PCI Express Revision	Gen 3.0
PCI Express Configurations *	Gen 3.0
Max # of PCI Express Lanes	24

### Package Specifications

Max CPU Configuration	2
T <sub>CASE</sub>	91°C
Sockets Supported	FC-LGA1356
Low Halogen Options Available	<a href="#">See MDDDS</a>

### Advanced Technologies

Intel® Turbo Boost Technology *	2.0
Intel® Hyper-Threading Technology *	 Yes
Intel® Virtualization Technology (VT-x) *	 Yes
Intel® Virtualization Technology for Directed I/O (VT-d) *	 Yes
Intel® VT-x with Extended Page Tables (EPT) *	 Yes
Intel® 64 *	 Yes
Enhanced Intel SpeedStep® Technology	 Yes
Intel® Flex Memory Access	No
Intel® Identity Protection Technology *	No

### Intel® Data Protection Technology


AES New Instructions	 Yes
Trusted Execution Technology *	 Yes

### Intel® Platform Protection Technology

Execute Disable Bit *	 Yes
-----------------------	---

## Compare

## Related Products

[Intel® Xeon® Processor E5 Family](#)[Intel® Xeon® Processor E5-2400 Product Family](#)[Products formerly Sandy Bridge EN](#)[Visit the Embedded Design Center >](#)

## Quick Links

[Export Full Specifications >](#)[Search Distributors >](#)[Software Downloads >](#)[Support Overview >](#)[Search all of intel.com >](#)

## PCN/MDDDS Information

**SR0M5**[919371: PCN | MDDDS](#)

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is", and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

"Intel classifications" consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company may be the exporter of record, and as such, your company is responsible for determining the correct classification of any item at the time of export.

Refer to Datasheet for formal definitions of product properties and features.

"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

Some products can support AES New Instructions with a Processor Configuration update, in particular, i7-2630QM/i7-2635QM, i7-2670QM/i7-2675QM, i5-2430M/i5-2435M, i5-2410M/i5-2415M. Please contact OEM for the BIOS that includes the latest Processor configuration update.

\*This feature may not be available on all computing systems. Please check with the system vendor to determine if your system delivers this feature, or reference the system specifications (motherboard, processor, chipset, power supply, HDD, graphics controller, memory, BIOS, drivers, virtual machine monitor-VMM, platform software, and/or operating system) for feature compatibility. Functionality, performance, and other benefits of this feature may vary depending on system configuration.

"Conflict free" and "conflict-free" means "DRC conflict free," which is defined by the U.S. Securities and Exchange Commission rules to mean products that do not contain conflict minerals (tin, tantalum, tungsten and/or gold) that directly or indirectly finance or benefit armed groups in the Democratic Republic of the Congo (DRC) or adjoining countries. Intel also uses the term "conflict-free" in a broader sense to refer to suppliers, supply chains, smelters and refiners whose sources of conflict minerals do not finance conflict in the DRC or adjoining countries. Intel processors manufactured before January 1, 2013 are not confirmed conflict free. The conflict free designation refers only to product manufactured after that date. For Intel Boxed Processors, the conflict free designation refers to the processor only, not to any additional included accessories, such as heat sinks/coolers.

See <http://www.intel.com/content/www/us/en/architecture-and-technology/hyper-threading/hyper-threading-technology.html?wapkw=hyper+threading> for more information including details on which processors support Intel® HT Technology.

Max Turbo Frequency refers to the maximum single-core processor frequency that can be achieved with Intel® Turbo Boost Technology. See [www.intel.com/technology/turboboost/](http://www.intel.com/technology/turboboost/) for more information.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.

Low Halogen: Applies only to brominated and chlorinated flame retardants (BFRs/CFRs) and PVC in the final product. Intel components as well as purchased components on the finished assembly meet JS-709 requirements, and the PCB / substrate meet IEC 61249-2-21 requirements. The replacement of halogenated flame retardants and/or PVC may not be better for the environment.

For benchmarking data see <http://www.intel.com/performance>.

Intel processor numbers are not a measure of performance. Processor numbers differentiate features within each processor family, not across different processor families. See <http://www.intel.com/content/www/us/en/processors/processor-numbers.html> for details.

Processors that support 64-bit computing on Intel® architecture require an Intel 64 architecture-enabled BIOS.

[Send us your feedback!](#)

About

Support

Legal

Social

Company Information

[Support Home](#)

[Terms of Use](#)

 [Intel Communities](#)

Investor Relations

[Download Center](#)

 [Trademarks](#)

 [Intel on Twitter](#)

Contact Us

[Product Specifications \(ARK\)](#)

 [Privacy](#)

 [Intel on Facebook](#)

Newsroom

 [Cookies](#)

 [Intel on LinkedIn](#)

Site Map

 [Intel on Instagram](#)

Jobs

 [Intel on YouTube](#)