

Part Number: 22-01-2266

KK® 254 Crimp Housing, 26 Circuits



Series image - Reference only

| | |
|---------------------|---------------------------------|
| Status: | OBsolete |
| Replacement: | Contact Molex |
| Series: | 6471 |
| Category: | Crimp Housings |
| Overview: | KK® Interconnect System - Molex |
| Engineering/Old PN: | 6471-26 |

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Go to Part Detail ▾

Mates With Part(s):

KK®254 PCB Headers [42375](#), [42377](#), [42376](#), [4030](#), [6373](#), [6410](#)

Use With:

[2759](#), [4809](#) KK® Crimp terminal

Specifications & Other Documents:

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com[EU ELV](#): Not Relevant[EU RoHS](#): Compliant[China RoHS](#): [REACH SVHC](#): Contains SVHC(2015 June 15): No[Low-Halogen Status](#): Low-Halogen

RoHS Certificate of Compliance (PDF)



Multiple Part Product Compliance Form

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Part Detail

COLLAPSE ALL

▼ General

| | |
|--------------|---|
| Status | Obsolete |
| Category | Crimp Housings |
| Series | 6471 |
| Application | Signal, Wire-to-Board |
| Overview | KK® Interconnect System - Molex |
| Product Name | KK® 254 |
| UPC | 800753740655 |

▼ Physical

| | |
|-------------------------------|---------------------------|
| Circuits (maximum) | 26 |
| Color - Resin | Natural (White) |
| Gender | Female |
| Glow-Wire Compliant | No |
| Material - Resin | Nylon |
| Net Weight | 2.500/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Polarized to Mating Part | No |
| Stackable | No |
| Temperature Range - Operating | See Product Specification |

▼ Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact [3.5A](#), [3.75A](#), [3.0A](#), [4.0A](#)

▼ Material Info

Old Part Number [6471-26](#)