


DO NOT SCALE


DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION

NOTES:

- 1 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED).
2 FOR USE ON STANDARD APPLICATOR (RIGHT-LEFT FEED)
3 FOR LOOSE-PIECE VERSIONS SEE DWG. 164169.
4 UNDERCOATING: 1,3µm Ni.
SELECTIVE : 0,8µm Au.
ZONE I : BRIGHT TIN/LEAD PLATED
5 UNDERCOATING: 1,27µm Ni.
SELECTIVE : 2,0µm Au.
REMAINDER : GOLDFLASH.
6 UNDERCOATING: 1,3µm Ni.
SELECTIVE : 0,8µm Au.
REMAINDER : GOLDFLASH.



WIRE RANGE :
20-24 AWG 0,2-0,56 mm²
INSULATION RANGE :
1,57 DIA. MAX.

SEE NOTE 5	STAINLESS STEEL	BRASS	1-164153-0	1
POST TINPLATED			164153-9	2
SEE NOTE 6			164153-8	2
SEE NOTE 4			164153-7	2
SEE NOTE 4			164153-6	1
PRETINNED			164153-5	2
PRETINNED			164153-4	1
POST TINPLATED			164153-2	1
SEE NOTE 6			164153-1	1
PLATING OF BODY	MATERIAL OF SLEEVE	MATERIAL OF BODY	PARTNUMBER	

CUSTOMER DRAWING					FOR REFERENCE ONLY WILL NOT BE UPDATED	
© COPYRIGHT 19- BY AMP HOLLAND B.V.						
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.						
THIS DRAWING IS UNPUBLISHED						
RELEASED FOR PUBLICATION						
AMP					AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands.	
NAME						
J EH-0077-92 JvL CvT 04-03-94					HDR SOCKET CONTACT TYPE XI (CRIMP SNAP-IN)	
LTR. REVISION RECORD DR. CHK. DATE						
DR. J.v.LIEMPT CHK. C.v.TILBURG APP. A.v.SOEST					DWG.No. C-164153	
DATE: 6 JAN 1993 DATE: 08-02-93 DATE: 08-02-93					REV.LTR. J SHEET 1 OF 1 A3	