

Housing - HC-D 7-TFL-57/M1PG11G/PA - 1772269


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sleeve housing, for single locking latch, height 48 mm, with screw connection, 1x Pg11, straight cable entry, material PA



Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 036935
Weight per Piece (excluding packing)	28.04 GRM
Custom tariff number	85472000
Country of origin	Germany

Technical data

Dimensions

Height	57 mm
Width	28 mm
Length	26.5 mm
Wrench size, union nut	18 mm
External cable diameter	7.5 mm ... 12.5 mm

Ambient conditions

Degree of protection of housing (IP)	IP54
	IP65 (with sealing screw)
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D7, D8, A3, A4, B5, HS2-D7
------	---

Housing - HC-D 7-TFL-57/M1PG11G/PA - 1772269

Technical data

General

Design	D7
Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable exits	1
Cable exit	Straight
Screw connection	With
Type of the screw connection	1x Pg11
Housing material	Polyamide
Housing surface material	PA, light gray
Cable gland material	Polyamide
Cable seal material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Housing - HC-D 7-TFL-57/M1PG11G/PA - 1772269

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 

Accessories

Accessories

Mounting material

Sealing screw - HC-D 7-DS-IP65 - 1686229



Sealing screw, for IP65 protection

Drawings

Dimensioned drawing

