

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

9907 Coax - Coaxial Cable - Thinnet 10Base2 Ethernet

For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (19x32) .037" tinned copper conductor, foam polyethylene insulation, Duobond® II (100% coverage) plus an overall tinned copper braid shield (93% coverage), PVC jacket.

Usage (Overall)

Suitable Applications:	Thin Ethernet
------------------------	---------------

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	19x32	TC - Tinned Copper	0.9398

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
FHDPE - Foam High Density Polyethylene	2.5908

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Dufoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	93

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 4.699 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

UL Temperature Rating: 60°C (UL AWM Style 1354)

Bulk Cable Weight: 34.229 Kg/Km

Max. Recommended Pulling Tension: 200.169 N

Min. Bend Radius/Minor Axis: 50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2, CM

CEC/C(UL) Specification: CM

AWM Specification: UL Style 1354 (30 V 60°C)

EU Directive 2011/65/EU (RoHS II): Yes

IEEE Specification: IEEE802.3 10Base2

Other Standards: ISO8802.3 10Base2

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

9907 Coax - Coaxial Cable - Thinnet 10Base2 Ethernet

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	DEC Part No. 17-01248-00
RG Type:	58A/U

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	82907, 89907

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)	Tolerance (Ohms)
50	+/- 2

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
83.3374

Nominal Velocity of Propagation:

VP (%)
80

Nominal Delay:

Delay (ns/m)
4.16687

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
28.8728

Maximum Loop Resistance:

Resistance (Ohm/km)
50.0024

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
19.0298

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	1.41083
10	4.2653
50	9.54771
100	13.7802
200	20.0141
400	29.2009
700	39.7001
900	45.6059
1000	48.5588

Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	
30 V RMS	UL AWM Style 1354

Notes (Overall)

Notes: Tape to bond at overlap area only. Tape is not designed to bond to dielectric core.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9907 E4XU1000	305 MT	10.886 KG	GRAY, LIGHT DEC		RG-58 TYPE COAX
9907 E4X1000	305 MT	11.340 KG	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X1640	500 MT	18.597 KG	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X2500	762 MT	28.350 KG	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X3280	1,000 MT	37.195 KG	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X500	152 MT	5.670 KG	GRAY, LIGHT DEC		RG-58 TYPE COAX

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

9907 Coax - Coaxial Cable - Thinnet 10Base2 Ethernet

9907 E4X5000	1,524 MT	56.699 KG	GRAY, LIGHT DEC	RG-58 TYPE COAX
--------------	----------	-----------	-----------------	-----------------

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-25-2012

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.