

MICRO SWITCH




FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

4SEI



NOTE-

- 1- MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .375±.002 CENTERS
- 2- ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3- WEIGHT OF SWITCH ONLY IS .26 OZ MAX, WEIGHT OF SWITCH WITH WIRE LEADS IS .6 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ——— 5-17 OZ
RELEASE FORCE ——— 4 OZ MIN
RELEASE TRAVEL ——— .004 MIN
DIFFERENTIAL TRAVEL ——— .004 MAX
OVERTRAVEL ——— .003 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A 250 VAC

UL Ⓢ

L4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		

WEIGHT

3

4SEI

DRAWING NUMBER

8

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4

4