


TOP VIEW




J Package – 8 Pin Ceramic DIP

N Package – 8 Pin Plastic DIP

D-8 Package – 8 Pin Plastic (150) SOIC

TOP VIEW



D-14 Package – 14 Pin Plastic (150) SOIC

CURRENT MODE REGULATING PULSE WIDTH MODULATORS

FEATURES

- Guaranteed $\pm 1\%$ reference voltage tolerance
- Guaranteed $\pm 10\%$ frequency tolerance
- Low start-up current ($< 500 \mu A$)
- Under voltage lockout with hysteresis
- Output state completely defined for all supply and input conditions
- Interchangeable with UC1844 and UC1845 series for improved operation
- 500kHz Oscillator operation
250kHz Output operation

Order Information

Part Number	J-Pack 8 Pin	N-Pack 8 Pin	D-8 8 Pin	D-14 14 Pin	Temp. Range	Note:
IP1844	✓				-55 to +125°C	To order, add the package identifier to the part number. eg. IP1844D-14 IP3845J
IP2844	✓	✓	✓	✓	-25 to +85°C	
IP3844	✓	✓	✓	✓	0 to +70°C	
IP1845	✓				-55 to +125°C	
IP2845	✓	✓	✓	✓	-25 to +85°C	
IP3845	✓	✓	✓	✓	0 to +70°C	

ABSOLUTE MAXIMUM RATINGS ($T_{case} = 25^\circ C$ unless otherwise stated)

V_{CC}	Supply Voltage	(low impedance source) ($I_{CC} < 30mA$)	+30V Self limiting
I_O	Output Current		$\pm 1A$
	Output Energy	(capacitive load)	5 μJ
	Analog Inputs	(pins 2 and 3)	-0.3V to $+V_{CC}$
	Error Amp Output Sink Current		10mA
P_D	Power Dissipation	$T_{amb} = 25^\circ C$ J, N Packages	1W
	Derate @ $T_{amb} > 50^\circ C$		10mW/ $^\circ C$
P_D	Power Dissipation	$T_{case} = 25^\circ C$ D Package	725mW
	Derate @ $T_{amb} > 50^\circ C$		7.25mW/ $^\circ C$
P_D	Power Dissipation	$T_{case} = 25^\circ C$ J, N Packages	2W
	Derate @ $T_{case} > 25^\circ C$		16mW/ $^\circ C$
T_{STG}	Storage Temperature Range		-65 to 150°C
T_L	Lead Temperature	(soldering, 10 seconds)	+300°C


DESCRIPTION

The IP1844 and IP1845 series of switching regulator control circuits contain all the functions necessary to implement off-line, current mode switching regulators, using a minimum number of external parts.

Functions included are voltage reference, error amplifier, current sense comparator, oscillator, totem-pole output driver and under-voltage lockout circuitry. In addition there is a toggle flip-flop which blanks the output on every second clock pulse, thereby ensuring that the duty cycle never exceeds 50%.

Although pin compatible with the UC1844 and UC1845 series, SEMELAB has incorporated several improvements in the IP1844 and IP1845 series allowing tighter and more complete specification of electrical performance .

BLOCK DIAGRAM



RECOMMENDED OPERATING CONDITIONS

V_{CC}	Supply Voltage	$\leq 30V$
I_O	Output Current	0 to $\pm 200mA$
	Analog Inputs (pins 2 and 3)	$-0.3V$ to $3V$
	Error Amp Output Sink Current	0 to $2mA$
	Operating Ambient Temperature Range	IP1844 , IP1845 IP2844 , IP2845 IP3844 , IP3845
		-55 to $125^{\circ}C$ -25 to $85^{\circ}C$ 0 to $70^{\circ}C$

ELECTRICAL CHARACTERISTICS (Over Full Operating Temperature Range unless otherwise stated)

Parameter	Test Conditions	IP1844/IP1845 IP2844/IP2845			IP3844 IP3845			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
REFERENCE SECTION								
Output Voltage	I _O = 1mA T _J = 25°C	4.95	5.00	5.05	4.90	5.00	5.10	V
Input Regulation	V _{CC} = 12V to 25V		6	20		6	20	mV
Output Regulation	I _O = 1mA to 20mA		6	25		6	25	
Temperature Stability			0.2	0.4		0.2	0.4	mV/°C
Total Output Variation	Line, Load, Temp	4.90		5.10	4.82		5.18	V
Output Noise Voltage	f = 10Hz to 10kHz T _J = 25°C		50			50		μV
Long Term Stability	T _J = 125°C @ 1000Hrs		5	25		5	25	mV
Output Short Circuit Current	V _{REF} = 0	30	80	160	30	80	160	mA
OSCILLATOR SECTION								
Frequency	T _J = 25°C	47	52	57	47	52	57	kHz
Voltage stability	V _{CC} = 12V to 25V		0.2	1		0.2	1	%
Temperature Stability	ΔT _A = Min to Max		5			5		%
Amplitude	V _{PIN4} Peak to Peak		1.7			1.7		V
Discharge Current	T _J = 25°C		8.3			8.3		mA
	ΔT _A = Min to Max		8			8		%
ERROR AMP SECTION								
Input Voltage	V _{PIN1} = 2.5V	2.45	2.50	2.55	2.42	2.50	2.58	V
Input Bias Current			−0.3	−1		−0.3	−2	μA
Open Loop Voltage Gain	V _O = 2V to 4V	65	90		65	90		dB
Unity Gain Bandwidth		0.7	1		0.7	1		MHz
Supply Voltage Rejection	V _{CC} = 12V to 25V	60	70		60	70		dB
Output Sink Current	V _{PIN2} = 2.7V V _{PIN1} = 1.1V	2	6		2	6		mA
Output Source Current	V _{PIN2} = 2.3V V _{PIN1} = 5.0V	−0.5	−0.8		−0.5	−0.8		
V _{OUT} High	V _{PIN2} = 2.3V R _L = 15kΩ	5.0	6.0		5.0	6.0		V
V _{OUT} Low	V _{PIN2} = 2.7V R _L = 15kΩ		0.7	1.1		0.7	1.1	

NOTES

1. Test Conditions unless otherwise stated:

$V_{CC} = 15\text{V}^*$, $R_T = 10\text{k}\Omega$, $C_T = 3.3\text{nF}$, $f = 52\text{kHz}$.

*Adjust V_{CC} above start threshold before setting at required level.

All specifications apply over the full operating temperature range unless otherwise stated. (See Ordering Information for further details).

ELECTRICAL CHARACTERISTICS (Over Full Operating Temperature Range unless otherwise stated)

Parameter	Test Conditions		IP1844/IP1845 IP2844/IP2845			IP3844 IP3845			Units
			Min.	Typ.	Max.	Min.	Typ.	Max.	
CURRENT SENSE SECTION									
Gain	See Notes 2,3		2.85	3	3.15	2.85	3	3.15	V/V
Maximum Input Signal	V _{PIN1} = 5.0V (Note 2)		0.9	1	1.1	0.9	1	1.1	V
Supply Voltage Rejection	V _C = 12V to 25V		60	70		60	70		dB
Input Bias Current				−2	−10		−2	−10	μA
Delay to Output				150	300		150	300	ns
OUTPUT SECTION									
Output Low Level	I _{SINK} = 20mA			0.1	0.4		0.1	0.4	V
	I _{SINK} = 200mA			1.5	2.2		1.5	2.2	
Output High Level	I _{SOURCE} = 20mA		13	13.5		13	13.5		V
	I _{SOURCE} = 200mA		12	13.5		12	13.5		
Rise Time	C _L = 1nF			50	150		50	150	ns
Fall Time	C _L = 1nF			50	150		50	150	
UVLO Saturation	V _{CC} = 6V I _L = 1mA			0.7	1.1		0.7	1.1	V
UNDER-VOLTAGE LOCKOUT SECTION									
Upper Threshold (V _{CC})	1844 Series		15	16	17	14.5	16	17.5	V
	1845 Series		7.8	8.4	9	7.8	8.4	9	
Lower Threshold (V _{CC})	1844 Series		9	10	11	8.5	10	11.5	V
	1845 Series		7	7.6	8.2	7	7.6	8.2	
TOTAL STANDBY CURRENT									
Start-up Current				0.3	0.5		0.3	0.5	mA
Operating Supply Current	V _{PIN2} = 0V	1844 Series		11	15		11	15	mA
	V _{PIN3} = 0V	1845 Series		14	17		14	17	
V _{CC} Zener Voltage	I _{CC} = 25mA		30	34	40	30	34	40	V
PWM SECTION									
Maximum Duty Cycle			47	48	50	46	48	50	%
Minimum Duty Cycle					0			0	

NOTES

1. Test Conditions unless otherwise stated:

V_{CC} = 15V*, R_T = 10kΩ, C_T = 3.3nF, f = 52kHz.

*Adjust V_{CC} above start threshold before setting at required level.

2. Parameter measured at trip point of latch with

V_{PIN2} = 0V

3. Gain defined as:

$$A = \frac{\Delta V_{PIN1}}{\Delta V_{PIN3}}$$


$$0 \leq V_{PIN3} \leq 0.8$$

All specifications apply over the full operating temperature range unless otherwise stated.

(See Ordering Information for further details).

APPLICATIONS INFORMATION

Oscillator Waveforms and Maximum Duty Cycle



Oscillator timing capacitor C_T is charged by V_{REF} through R_T and discharged by an internal current source. During the discharge time, the internal clock signal blanks the output to the low state. Selection of R_T and C_T therefore determines both oscillator frequency and maximum duty cycle.

Charge and discharge times are determined by the formulae:

$$t_c \approx 0.55 R_T C_T$$

$$t_d \approx R_T C_T \ln \left(\frac{.0063 R_T - 2.3}{.0063 - 4} \right)$$

$$\text{Resultant frequency } f = \frac{1}{(t_c + t_d)}$$

For $R_T > 5k\Omega$,

$$\text{Resultant frequency } f \approx \frac{1.8}{(R_T C_T)}$$

Open-Loop Laboratory Test Fixture

