


# CUSTOMER DRAWING



Product Revision		Product Dimensions			Cable Dimensions	
Product Name		L max	E min	φA min	φD min	φD max
D-436-08	L	34.7 (1.365)	7.7 (0.305)	3.8 (0.150)	0.65 (0.250)	3.8 (0.150)
D-436-09	L	34.8 (1.370)	7.7 (0.305)	6.1 (0.240)	1.25 (0.050)	6.1 (0.240)
D-436-10	C	35 (1.380)	7.7 (0.305)	7.9 (0.310)	2.55 (0.100)	7.9 (0.310)


## MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
2. SEALING RING: Immersion resistant thermoplastic. Color:gray.

## APPLICATION

1. These parts are designed to provide an immersion resistant seal on 1 to 1 splices made of wires having an insulation rated for at least +135°C.
2. Temperature range: -55°C to +150°C. Parts may be installed by convection heating.

Cable dimension:



\* A trademark of Raychem Corporation.

 <b>TE Connectivity</b>		<b>RAYCHEM DEVICES</b>	<b>TITLE: SEALING SLEEVE</b>			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.			DOCUMENT NO.: <b>D-436-08/-10</b>			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	Raychem reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.			REVISED PER ECO: <b>13-002343</b>	
DRAWN BY: <b>T.NGUYEN</b>	DATE: <b>02/06/2013</b>	REVISION: <b>B</b>	SCALE: None	SIZE: <b>A</b>	SHEET: <b>1 of 1</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D-436-09](#)