






- 1 MATERIAL:
SHELL & CONTACTS- COPPER ALLOY.
HOUSING- UL 94V-0 RATED, THERMOPLASTIC, COLOR SEE TABLE.
- 2 PLATING:
CONTACTS- 0.076um MINIMUM GOLD OVER 0.76um MINIMUM PALLADIUM-NICKEL ON MATING AREA.
3.8um MINIMUM MATTE TIN ON SOLDER TAILS.
BOTH OVER 1.27um MINIMUM NICKEL.
CONTACT ALTERNATE PLATING: 0.76um MIN GOLD ON MATING AREA, 3.80um MIN MATTE TIN ON SOLDER TAILS, BOTH OVER 1.27um MIN NICKEL.
SHELL: 2~5um MINIMUM BRIGHT TIN
- 3 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.

TAPE&REEL		YES		NATURAL		6364372-3	
TUBE		YES		NATURAL		6364372-2	
TUBE		NO		BLACK		6364372-1	
PACKAGING		HIGH TEMPERATURE COMPATIBLE		HOUSING COLOR		PART NUMBER	

DRAWING IS A CONTROLLED DOCUMENT.		DWN J.JIANG 12APR2004		 TE Connectivity							
		CHK S.YAO 12APR04									
DIMENSIONS: mm		APVD J.QU 12APR04		NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, 4POSITION, THRU-HOLE, USB							
		PRODUCT SPEC									
		APPLICATION SPEC									
		—									
		—									
TOLERANCES UNLESS OTHERWISE SPECIFIED:				SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
0 PLC ± -		WEIGHT 0		A2		00779		C=6364372		—	
1 PLC ± -		CUSTOMER DRAWING				SCALE 5:1		SHEET 1 of 1		REV A1	
2 PLC ± 0.25											
3 PLC ± -											
4 PLC ± -											
ANGLES ± -											
FINISH											
											
											