



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AB5	REVISED PER ECO-13-005565	02APR13	KH	JO



12 ROHS 2002/95/EC COMPLIANT

RECOMMENDED PC BOARD HOLE PATTERN
PC BOARD THICKNESS 1.57[.062]



- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE
- 2 CONTACT: DUPLEX PLATED 0.76 μ m[.000030] GOLD IN CONTACT AREA, 3.81–7.62 μ m[.000150–.000300] BRIGHT TIN–LEAD ON LEADS, ALL OVER 1.27 μ m[.000050] MINIMUM NICKEL
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY – NOT TO CONTACT LOCATIONS
- 4 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN,EITHER SIDE.
- 5 TOLERANCE IS NON–CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO.
- 7 POINT–OF–MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).
- 8 POINT–OF–CONTACT DIMENSION.
- 9 TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- 10 NO PART NUMBER MARKING REQUIRED FOR THIS PART.
- 11 CONTACT:DUPLEX PLATED 0.76 MICROMETERS(.000030) MIN GOLD IN CONTACT AREA,3.81–7.62 MICROMETERS(.000150–.000300) MATTE TIN ON LEADS, ALL OVER 1.27 MICROMETERS (.000050) MINIMUM NICKEL.

SUPERSEDED BY 8-534267-4		96.52[3.800]	99.06[3.900]	78	4-534267-0	
		91.44[3.600]	93.98[3.700]	74	3-534267-9	
		88.90[3.500]	91.44[3.600]	72	3-534267-8	
		86.36[3.400]	88.90[3.500]	70	3-534267-7	
		83.82[3.300]	86.36[3.400]	68	3-534267-6	
		81.28[3.200]	83.82[3.300]	66	3-534267-5	
		78.74[3.100]	81.28[3.200]	64	3-534267-4	
		76.20[3.000]	78.74[3.100]	62	3-534267-3	
		71.12[2.800]	73.66[2.900]	58	3-534267-2	
		68.58[2.700]	71.12[2.800]	56	3-534267-1	
		66.04[2.600]	68.58[2.700]	54	3-534267-0	
		63.50[2.500]	66.04[2.600]	52	2-534267-9	
		55.88[2.200]	58.42[2.300]	46	2-534267-8	
		53.34[2.100]	55.88[2.200]	44	2-534267-7	
		50.80[2.000]	53.34[2.100]	42	2-534267-6	
		45.72[1.800]	48.26[1.900]	38	2-534267-5	
		40.64[1.600]	43.18[1.700]	34	2-534267-4	
		38.10[1.500]	40.64[1.600]	32	2-534267-3	
		33.02[1.300]	35.56[1.400]	28	2-534267-2	
			25.40[1.000]	27.94[1.100]	22	2-534267-1
		12.70[.500]	15.24[.600]	12	2-534267-0	
		17.78[.700]	20.32[.800]	16	1-534267-9	
		60.96[2.400]	63.50[2.500]	50	1-534267-8	
		2.54[.100]	5.08[.200]	4	1-534267-7	
		93.98[3.700]	96.52[3.800]	76	1-534267-6	
		43.18[1.700]	45.72[1.800]	36	1-534267-5	
		5.08[.200]	7.62[.300]	6	1-534267-4	
				2.54[.100]	2	 1-534267-3
			35.56[1.400]	38.10[1.500]	30	1-534267-2
		58.42[2.300]	60.96[2.400]	48	1-534267-1	
		20.32[.800]	22.86[.900]	18	1-534267-0	
		27.94[1.100]	30.48[1.200]	24	534267-9	
		73.66[2.900]	76.20[3.000]	60	534267-8	
		48.26[1.900]	50.80[2.000]	40	534267-7	
		30.48[1.200]	33.02[1.300]	26	534267-6	
			7.62[.300]	10.16[.400]	8	534267-5
			99.06[3.900]	101.60[4.000]	80	534267-4
		10.16[.400]	12.70[.500]	10	534267-3	
		22.86[.900]	25.40[1.000]	20	534267-2	
		15.24[.600]	17.78[.700]	14	534267-1	
	FINISH	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06NOV2002 M.BINNER CHK 06NOV02 J.OLSON APVO 06NOV02 J.OLSON PRODUCT SPEC 108-25022 APPLICATION SPEC 114-25018 WEIGHT -		 TE Connectivity RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME SIZE CAGE CODE DRAWING NO RESTRICTED TO		A2 00779 C-534267 -	
MATERIAL 		FINISH 		SCALE 4:1 SHEET 1 of 2 REV AB5		CUSTOMER DRAWING	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

AD00

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

D

C

B

A

11

96.52

[3.800]

11

91.44

[3.600]

11

88.90

[3.500]

11

86.36

[3.400]

11

83.82

[3.300]

11

81.28

[3.200]

11

78.74

[3.100]

11

76.20

[3.000]

11

71.12

[2.800]

11

68.58

[2.700]

11

66.04

[2.600]

11

63.50

[2.500]

11

55.88

[2.200]

11

53.34

[2.100]

11

50.80

[2.000]

11

45.72

[1.800]

11

40.64

[1.600]

11

38.10

[1.500]

11

33.02

[1.300]

11

25.40

[1.000]

11

12.70

[.500]

11

17.78

[.700]

10

60.96

[2.400]

11

2.54

[.100]

11

93.98

[3.700]

11

43.18

[1.700]

10

5.08

[.200]

11

-

11

35.56

[1.400]

11

58.42

[2.300]

11

20.32

[.800]

11

27.94

[1.100]

11

73.66

[2.900]

11

48.26

[1.900]

11

30.48

[1.200]

10

7.62

[.300]

11

99.06

[3.900]

10

10.16

[.400]

11

22.86

[.900]

11

15.24

[.600]

FINISH

B

A

NO OF POSN

PART NUMBER

10

OBSOLETE

10

534267

10

534267

10

534267

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13[.005]

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

11

2

DWN
M.BINNER

CHK
J.OLSON

APVD
J.OLSON

PRODUCT SPEC
108-25022

APPLICATION SPEC
114-25018

WEIGHT
-

CUSTOMER DRAWING

06NOV2002

06NOV02

06NOV02

NAME
RECEPTACLE ASSEMBLY, MOD IV,
DOUBLE ROW, DUAL ENTRY, .100X.100CL,
VERTICAL MOUNT, AMPMODU

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=534267

RESTRICTED TO
-

SCALE
1:1

SHEET
2 of 2

REV
AB5

TE Connectivity

1471-9 (3/11)