

L-7104SGD-14V

SUPER BRIGHT GREEN


Features

- LOW POWER CONSUMPTION.
- POPULAR T-1 DIAMETER PACKAGE.
- GENERAL PURPOSE LEADS.
- RELIABLE AND RUGGED.
- LONG LIFE - SOLID STATE RELIABILITY.
- AVAILABLE ON TAPE AND REEL.
- 14V INTERNAL RESISTOR.
- RoHS COMPLIANT.

Description

The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions



Notes:

Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is ± 0.25 (0.01") unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. Specifications are subject to change without notice.

Kingbright

Selection Guide

Part No.	Dice	Lens Type	IV (mcd) V=14V		Viewing Angle
			Min.	Typ.	
L-7104SGD-14V	SUPER BRIGHT GREEN (GaP)	GREEN DIFFUSED	8	20	40°

Note:

1. $\theta_{1/2}$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at $T_A=25^\circ C$


Symbol	Parameter	Device	Typ.	Max.	Units	Test Conditions
λ_{peak}	Peak Wavelength	Super Bright Green	565		nm	$V_F=14V$
λ_D	Dominant Wavelength	Super Bright Green	568		nm	$V_F=14V$
$\Delta\lambda_{1/2}$	Spectral Line Half-width	Super Bright Green	30		nm	$V_F=14V$
I_F	Forward Current	Super Bright Green	10.5	13.5	mA	$V_F=14V$
I_R	Reverse Current	Super Bright Green		10	uA	$V_R = 5V$

Absolute Maximum Ratings at $T_A=25^\circ C$

Parameter	Super Bright Green	Units
Power dissipation	160	mW
Forward Voltage	16	V
Reverse Voltage	5	V
Operating Temperature	-40°C To +70°C	
Storage Temperature	-40°C To +85°C	
Lead Solder Temperature[1]	260°C For 3 Seconds	
Lead Solder Temperature[2]	260°C For 5 Seconds	





Notes:

1. 2mm below package base.
2. 5mm below package base.



Super Bright Green

L-7104SGD-14V



Remarks:

If special sorting is required (e.g. binning based on luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

1. Wavelength: +/-1nm
2. Luminous Intensity: +/-15%

Note: Accuracy may depend on the sorting parameters.