

OBSOLETE

SPECIFICATIONS:

MATERIAL:-

INSULATOR: LCP (UL94V-0)

CENTER CONTACT: BRASS

GROUND CONTACT: BRASS

FINISH:-

CENTER CONTACT: GOLD PLATING

GROUND CONTACT: SILVER PLATING

ELECTRICAL:-

VOLTAGE PROOF: 200 V AC FOR 1 MINUTE

CONTACT RESISTANCE: 20 mΩ MAX. FOR CENTER CONTACT

10 mΩ MAX. FOR OUTSIDE CONTACT

INSULATION RESISTANCE: 500 MΩ MIN.

MEASURED AT 100 V DC

MECHANICAL:-

WITHDRAWAL FORCE: 0.15N MIN.

ENVIRONMENTAL:-





TEMPERATURE RANGE: -40°C TO +90°C

NOTES: ALL DIMENSIONS AND NOTES

MARKED ✕ ARE CRITICAL AND

MUST BE CHECKED IN ACCORDANCE

WITH QUALITY DOC. Q1-02A

RECOMMENDED PCB PATTERN

Allan	1	01.08.06	-
NAME	ISS.	DATE	C/NOTE

APPROVED: _____

CHECKED: *P. Pan*

DRAWN: Allan

CUSTOMER REF.: _____

ASSEMBLY DRG: _____

NOTES:

REMOVE ALL BURRS & SHARP EDGES 0.25 MAX
MACHINE FILLET R0.25 MAX.ALL DIAS. TO BE CONCENTRIC WITHIN .125 T.I.R
INTERPRETATION PER MIL STD 8 10 & 12**HARWIN**HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.comHARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.ukHARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sgTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE NOTES

FINISH:

SEE NOTES

S/AREA:

mm²

TITLE:

COAX. MICROWAVE CONNECTOR
(O/D 2.1)

DRAWING NUMBER:

UMCR-1150005R

SHT
1
OF 1