

C631308025 Cable Assemblies - CAT6+ Modular Cord



For more Information
please call

1-800-Belden1

**General Description:**

CAT6+ Pigtail, Non-Bonded-Pair, 4 Pair, 23 AWG Solid, CMR, T568B-Open, Gray, 25 ft. (7.6 m).

Usage (Overall)

Suitable Applications:	IBDN System 4800, IBDN System 3600, IBDN System 2400, TIA Category 6, ISO Class E, 1000BASE-T
Related Parts:	CAT6+ Modular Jacks, CAT6+ Couplers, CAT6+ Patch Panels

Multi Conductor**Physical Characteristics****Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Color Code Chart:

Color
Gray

Overall Cabling

Overall Cabling Fillers:	Cross Web
---------------------------------	-----------

Overall Diameter

Overall Nominal Diameter:	0.238 in.
----------------------------------	-----------

Physical Characteristics (Connectivity)**Materials**

Materials:

Description	Type	Material
Plug	RJ45	Polycarbonate
Boot		Rubber
Front Connection	Blades	Phosphor Bronze with 50u inch Gold over Nickel Plating

Color

Boot Color:	Translucent
--------------------	-------------

Wiring Scheme

Wiring Scheme:	T568B-Open
-----------------------	------------

Weight

Weight:	0.675 lbs.
----------------	------------

Packaging

Packaging:	Individually packaged in a clear plastic bag.
-------------------	---

Mechanical Characteristics (Connectivity)

Plug / Jack Compatibility:	RJ45
-----------------------------------	------

Termination Interface:

Termination	Connection	Durabilities
RJ45	Mated Connection	750 Cycles

Storage Temperature Range:	-40°C To +70°C
-----------------------------------	----------------

C631308025 Cable Assemblies - CAT6+ Modular Cord

Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C
Max. Recommended Pull Tension:	25 lbs.
Min. Bend Radius (Overall Cable):	1.040 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating:	Riser
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
MIL Order #39 (China RoHS):	EUP 50
Telecommunications Standards:	ISO/IEC 11801:2002 Ed.2
Safety Listing:	Bi-national Standard Listed

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Performance Table 1:

Frequency (MHz)	Max. Insertion Loss TIA* (dB)	Max. Insertion Loss Belden (dB)	Min. PSNEXT TIA* (dB)	Min. PSNEXT Belden (dB)	Min. PSACRF TIA* (dB)	Min. PSACRF Belden (dB)
1.000	2.400	2.000	72.300	73.300	64.800	67.800
4.000	4.500	3.700	63.300	64.300	52.800	55.800
8.000	6.400	5.200	58.800	61.300	46.700	49.700
10.000	7.100	5.900	57.300	59.800	44.800	47.800
16.000	9.100	7.400	54.200	56.600	40.700	43.700
20.000	10.200	8.300	52.800	55.100	38.800	41.800
25.000	11.400	9.300	51.300	53.500	36.800	39.800
31.250	12.800	10.400	49.900	52.000	34.900	37.900
62.500	18.500	14.900	45.400	47.100	28.900	31.900
100.000	23.800	19.000	42.300	43.800	24.800	27.800
200.000	34.800	27.500	37.800	38.900	18.800	21.800
250.000	39.400	31.000	36.300	37.300	16.800	19.800
300.000		34.200		36.100		18.300

Performance Table - Footnote:

100 Meter Cable Specifications - * TIA-EIA-568-C.2 Category 6 Standard ----- PSACRF is formally PSELFEXT

Performance Table 2:

Frequency (MHz)	Min. Return Loss TIA* (dB)	Min. Return Loss Belden (dB)	Min. Balanced TCL TIA* (dB)	Min. Balanced TCL Belden (dB)
1.000	20.000	20.000	40.000	40.000
4.000	23.000	23.000	40.000	40.000
8.000	24.500	24.500	40.000	40.000
10.000	25.000	25.000	40.000	40.000
16.000	25.000	25.000	38.000	38.000
20.000	25.000	25.000	37.000	37.000
25.000	24.200	24.300	36.000	36.000
31.250	23.300	23.600	35.100	35.100
62.500	20.700	21.500	32.000	32.000
100.000	19.000	20.800	30.000	30.000
200.000	16.400	18.700	27.000	27.000
250.000	15.600	18.000	26.000	26.000
300.000		17.500		

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max. Contact Resistance:	20 m-Ohm

Electrical Characteristics (Overall)

Labeling

Labeling:	Labeling: Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length.
-----------	---

C631308025 Cable Assemblies - CAT6+ Modular Cord

Notes (Overall)

Notes: C601106010 is subdivided as following C6-01-1-06-010 C6 stands for performance, 01 stands for cable type, 1 stands for termination type, 06 stands for color, 010 stands for length Use last 3 digits of the code to specify length in feet - 001-015 ft in increments of 1 ft than 20 ft or 25 ft

Product Family

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
C631308025	1 EA	0.675 LB	NONE		PIGTAIL-B CAT6+ CMR GRY 25FT

Revision Number: 0 Revision Date: 12-05-2011

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.