



#### Series Datasheet – BE Reed Relays

#### www.standexmeder.com

# BE Series Reed Relays



- Features: Latching or High IR, Plastic or Metal Housing, High Life Expectancy, Variety of Pin Out Schemes
- Applications: General purpose, Test Equipment, Medical equipment & Others
- Markets: Telecommunications, Medical, Test & Measurement & Others



Customer Options					
Switch Model	66	85	90	Unit	
Rated Power (max.) Any DC combination of V&A not to exceed their individual max.'s	10	100	10	W	
Switching Voltage (max.) DC or peak AC	200	1,000	175	V	
Switching Current (max.) DC or peak AC	0.5	1.0	0.5	А	
Carry Current (max.) DC or peak AC	1.25	2.5	1.2	А	
Contact Resistance (max.) @ 0.5V & 50mA	150	150	150	mOhm	
Breakdown Voltage (min.) According to EN60255-5	0.225	2.5	0.2	kVDC	
Operating Time (max.) Incl. Bounce; Measured with w/ Nominal Voltage	0.5	1.1	0.7	ms	
Release Time (max.) Measured with no Coil Excitation	0.1	0.1	1.5	ms	
Insulation Resistance (typ.) Rh<45%, 100V Test Voltage	10 <sup>10</sup>	10 <sup>12</sup>	10 <sup>9</sup>	Ohm	
Capacitance (typ.) @ 10kHz across open Switch	0.2	0.5	1.0	pF	



USA: +1.866.782.6339 Europe: +49.7731.8399.0 Asia: +86.21.37820625 | salesusa@standexmeder.com | info@standexmeder.com | salesasia@standexmeder.com



#### Series Datasheet – BE Reed Relays

#### www.standexmeder.com

Coil Data				5 11 1 1/ 1:	5 0 1 1/4 1/4	
Contact Form	Switch Model	Coil Voltage (nom.)	Coil Resistance (typ.)	Pull-In Voltage (max.)	Drop-Out Voltage (min.)	Nominal Coil Power (typ.)
Ur	nit	VDC	Ohm	VDC	VDC	mW
1A -	66	05	140 (345)	3.5	0.75	179 (72)
		12	855 (2,145)	8.4	1.8	168 (67)
		24	3,285 (7,845)	16.8	3.6	175 (73)
	85	05	105 (140)	3.5	0.75	238 (179)
		12	620 (1,000)	8.4	1.8	232 (144)
		24	1,400 (2,300)	16.8	3.6	411 (250)
1B	66	12	(1,100)	8.4	1.8	131
		24	(4,240)	16.8	3.6	136
1C 9	90	12	2,145	8.4	1.8	67
	90	24	7,845	16,8	3.6	73
2A	66	12	445 (1,100)	8.4	1.8	324 (131)
		24	1,700 (4,240)	16.8	3.6	339 (136)
	85	05	70 (110)	3.5	0.75	357 (227)
		12	420 (600)	8.4	1.8	343 (240)
		24	1,080 (1,600)	16.8	3.6	533 (360)
2A + 2B	85	05	49	3.5	0.25	510
		12	303	8.4	0.7	475
		24	1,140	16.8	1.4	505

The Pull-In / Drop-Out Voltage and Coil Resistance will change at rate of 0.4% per  $^{\circ}$ C The figures in brackets are for realys in metal casing.


<b>Environmental Data</b>	Unit	
Shock Resistance (max.) 1/2 sine wave duration 11ms	50	g
Vibration Resistance (max.)	20	g
Operating Temperature	-20 to 70	°C
Storage Temperature	-35 to 95	°C
Soldering Temperature (max.) 5 sec. max.	260	°C

#### **Handling & Assembly Instructions**

- Switching inductive and/or capacitive loads create voltage and/or current peaks, which may damage the relay.

  Protective circuits need to be used.
- External magnetic fields needs to be taken into consideration, including a too high packing density.
   This may influence the relays' electrical characteristics.
- Mechanical shock impacts e.g. dropping the relays may cause immediate or post-installation failure.
- Wave soldering: maximum 260°/5 seconds.
- Reflow soldering: Recommendations given by the soldering paste manufacturer need to be considered as well as the temperature limits of other components/processes.







USA: +1.866.782.6339 Europe: +49.7731.8399.0 Asia: +86.21.37820625 | salesusa@standexmeder.com | info@standexmeder.com | salesasia@standexmeder.com



### Series Datasheet – BE Reed Relays

#### www.standexmeder.com

Glossary Contact Form				
Form A	NO = Normally Open Contacts SPST = Single Pole Single Throw			
Form B	NC = Normally Closed Contacts SPST = Single Pole Single Throw			
Form C	Changeover SPDT = Single Pole Double Throw			






#### Pin Out


## View from top of component 2.54mm [0.10"] pitch grid

10




ONLY WHEN USING THE MERCURY WETTED (88) SWITCH

11




14








20



MERCURY WETTED (88) SWITCH

23





USA: +1.866.782.6339 Europe: +49.7731.8399.0 Asia: +86.21.37820625 | salesusa@standexmeder.com | info@standexmeder.com | salesasia@standexmeder.com