

4


3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C 2	REVISED PER ECO-11-005150	29MAR2011	RK	HMR

TE LOGO, TE CONNECTIVITY PN, VALUE
TOLERANCE & DATE CODE



1 FOR FURTHER INFORMATION SEE DATA SHEET FOR
HS SERIES-ALUMINIUM HOUSED RESISTORS

2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF

3 TECHNICAL SPECIFICATION

DISSIPATION AT 25°C : 25 WATTS MOUNTED
ON STANDARD HEATSINK

BS OHMIC RANGE : R051 TO 27K



STABILITY : $\Delta R < = 1\%$ PER 1000hrs

ISOLATION VOLTAGE : 2500V DC/AC pk


MAX WORKING VOLTAGE : 500V DC/AC rms

TEMP COEFFICIENT : > 1R0 50ppm
> 100R 25ppm

CLIMATIC CATEGORY : 55/200/56



RoHS Compliant



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	29.SEP.05	 TE Connectivity		
		CHK	30.SEP.05			
		J CATCHPOLE	30.SEP.05	NAME HSA25 METAL CLAD RESISTOR		
		APVD	30.SEP.05			
		J CATCHPOLE		SIZE A3		
		PRODUCT SPEC				
		-		CAGE CODE 00779		
		APPLICATION SPEC				
		-		DRAWING NO C-1625971		
		WEIGHT	-			
		CUSTOMER DRAWING		RESTRICTED TO -		
				SCALE 3:1		
				SHEET 1 OF 1		
				REV C2		