

SURGE PROTECTORS

SURGE STRIPS

GC Electronics offers a variety of Surge Protection Power Strips to meet your needs.

Electrical Ratings: 125V/15A/1875W
Response Time: ≤ 1 nano second



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8

Retail Part No.	Figure Number	Number Of Outlets	Description	Cord Specs	Color	15 amp Breaker	D-DSS Coax Tele	Max Joules
64-663	1	4	Surge Strip	3' - 14/3	Gray	Y	None	90 J
64-830	2	5	Surge EMI/RFI Strip	4' - 14/3	Ivory	Y	C - 46 J	200 J
64-661	3	6	Surge Strip	4' - 14/3	Gray	Y	None	90 J
64-6610	3	6	Surge Strip	10' - 14/3	Gray	Y	None	90 J
64-6615	3	6	Surge Strip	15' - 14/3	Gray	Y	None	90 J
64-668	3	6	Surge Strip	4' - 14/3	Gray	Y	None	270 J
64-631	4	6	Metal Surge Strip	4' - 14/3	Gray	Y	None	450 J
64-632	4	6	Metal Surge Strip	15' - 14/3	Gray	Y	None	450 J
64-804	5	6	Surge EMI/RFI Strip	4' - 14/3	Gray	Y	T - 72 J	540 J
64-667	6	6	Surge EMI/RFI Strip	4' - 14/3	Gray	N	None	540 J
64-669	7	6	PC Smart Surge	6' - 14/3	Gray	Y	T - 160 J	1100 J
64-670	8	10	Home Ent. System Surge	6' - 14/3	Gray	Y	D, C, T-160 J	1665 J

Retail Part No.	Figure Number	Max Surge Voltage	Max Spike Current	Clamping Voltage	Line Protection (mov)	EMI/RFI Filtering Specs	Agency Listing
64-663	1	6500 V	4500 A	330 V	H-N	n/a	UL, CSA
64-830	2	6500 V	4500 A	400 V	N-G, H-G	100 KHz-30 MHz/Up to 40 dB	UL, CSA
64-661	3	6500 V	4500 A	330 V	H-N	n/a	UL, CSA
64-6610	3	6500 V	4500 A	330 V	H-N	n/a	UL, CSA
64-6615	3	6500 V	4500 A	330 V	H-N	n/a	UL, CSA
64-668	3	6000 V	13,500 A	330 V	H-N, N-G, H-G	100 KHz-50 MHz/Up to 52 dB	UL, CUL
64-631	4	6000 V	13,500 A	330 V	H-N, N-G, H-G	100 KHz-50 MHz/Up to 40 dB	UL, CUL
64-632	4	6000 V	13,500 A	330 V	H-N, N-G, H-G	100 KHz-50 MHz/Up to 40 dB	UL, CUL
64-804	5	6000 V	4500 A	330 V	H-N, N-G, H-G	150 KHz-100 MHz/Up to 40 dB	UL
64-667	6	6000 V	13000 A	330 V	H-N, N-G, H-G	150 KHz-100 MHz/Up to 40 dB	UL, CUL
64-669	7	6000 V	26000 A	330 V	H-N, N-G, H-G	150 KHz-100 MHz/Up to 40 dB	UL, CUL
64-670	8	6000 V	39000 A	330 V	H-N, N-G, H-G	150 KHz-100 MHz/Up to 40 dB	UL, CUL