




3-Pin Threaded Pico-Style Cables

Cable: PVC jacket, 3 x 24 AWG

Conductors: PUR (polyurethane) body, nickel-plated brass coupling nut, gold-plated contacts

Voltage/Current Rating: 125V ac/300V dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1=Brown 3=Blue 4=Black	Straight	PKG3M-2	2 m		• T8 • VS1 • VS2 • VS3 • VS4 • SLM • IP68 Sealed Ring Lights (Nickel-plated) • IP68 Sealed Ring[†] Lights (stainless steel) • On-axis Lights
		PKG3M-4 [†]	4 m		
		PKG3M-7 [†]	7 m		
		PKG3M-9	9 m		
		PKG3M-10 [†]	10 m		
	Right-Angle	PKW3M-2	2 m		
PKW3M-9		9 m			

† IP68 stainless steel models require a cable with a stainless steel connector. For a stainless steel connector, add **V** to the model number (example, **PKG3M-4V**).




3-Pin Pico-Style Splitter Cables

Cable: PVC jacket, 3 x 24 AWG

Conductors: PUR (polyurethane) body, nickel-plated brass coupling nut, gold-plated contacts

Voltage/Current Rating: 125V ac/300V dc, 4.0 A

Temperature: +105° C

Connections					Used With
Pinout	Model	Branches	Trunks		
 Female 1=Brown 3=Blue 4=Black	CSB-M831M831	3-Pin Pico QD 2 x 0.2 m Female	0.2 m Male	 Male	• Ring Lights • Spot Lights • Area Lights • Backlights
					




4-Pin Snap-on Pico-Style Cables

Cable: PVC jacket, 3 x 26 AWG

Conductors: PUR (polyurethane) body, snap lock, POM locking sleeve (right-angle only), gold-plated contacts

Voltage/Current Rating: 125V ac/300V dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
 Female 1 = Brown 2 = White 3 = Blue 4 = Black	Straight	PKG4-2	2 m		• MINI-BEAM 2 • QS12 • QS18 • Q20 • D12 • D10A
	Right-Angle	PKW4Z-2	2 m		




4-Pin Snap-On Pico-Style Cables with Shield

Cable: PVC jacket, 4 x 26 AWG with 26 AWG drain wire

Conductors: PUR (polyurethane) body, snap lock, POM locking sleeve (right-angle only), nickel-plated brass coupling nut, gold-plated contacts

Voltage/Current Rating: 125V ac/300V dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black	Straight	PKG4S-2	2 m		• QS18U
	Right-Angle	PKW4ZS-2	2 m		




4-Pin Threaded Pico-Style Cables

Cable: PVC jacket, 4 x 26 AWG

Conductors: PUR (polyurethane) body, nickel-plated brass coupling nut, gold-plated contacts

Voltage/Current Rating: 125V ac/dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With	
Female  1 = Brown 2 = White 3 = Blue 4 = Black	Straight	PKG4M-2	2 m		• Q12 • Q20	
		PKG4M-9	9 m			
	Right-Angle	PKW4M-2	2 m			
		PKW4M-9	9 m			




6-Pin Snap-On Pico-Style Cables

Cable: PVC jacket, 6 x 26 AWG

Conductors: PUR (polyurethane) body, POM locking sleeve, gold-plated contacts

Voltage/Current Rating: 125V ac/dc, 2.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 4 = Black 2 = White 5 = Gray 3 = Blue 6 = Pink	Straight	PKG6Z-2	2 m		• D10 • FI22
		PKG6Z-9	9 m		
	Right-Angle	PKW6Z-2	2 m		
		PKW6Z-9	9 m		




4-Pin Euro-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black	Straight	MQDC-406	2 m		• Q12 • M12 • QS18 • Q20 • OMNI-BEAM (QDH suffix) • Q45 dc sensors (Q5 suffix) • MINI-BEAM dc SM312 sensors • S18, M18, T18, Q25, S30, T30, Q40 • QM42 • QL50/QL55 • SLM • T18U • K50 • K80 • PVA • VTB and STB • EZ-LIGHT
		MQDC-415	5 m		
		MQDC-430	9 m		
	Right-Angle	MQDC-406RA	2 m		
		MQDC-415RA	5 m		
		MQDC-430RA	9 m		




4-Pin Euro-Style Cables with Shield

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black	Straight	MQDEC2-406	2 m		• QS18U
		MQDEC2-415	5 m		
		MQDEC2-430	9 m		
	Right-Angle	MQDEC2-406RA	2 m		
		MQDEC2-415RA	5 m		
		MQDEC2-430RA	9 m		




4-Pin Euro-Style Cables (for use with NAMUR sensors)

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = Blue	Straight	MQD9-406	2 m		• MINI-BEAM & Q45 NAMUR sensors
		MQD9-415	5 m		
	Right-Angle	MQD9-406RA	2 m		
		MQD9-415RA	5 m		






4-Pin Euro-Style Cables–Double Ended

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Male  Female  1 = Brown 2 = White 3 = Blue 4 = Black	Male Straight/ Female Straight	MQDEC-403SS	1 m	 	• M12 • QS18 • Q20 • OMNI-BEAM (QDH suffix) • Q45 dc sensors (Q5 suffix) • MINI-BEAM dc SM312 sensors • S18, M18, T18, Q25, S30, T30, Q40 • QM42 • T18U • K50 • K80 • PVA • VTB and STB • EZ-LIGHT
		MQDEC-406SS	2 m		
		MQDEC-412SS	4 m		
		MQDEC-420SS	7 m		
		MQDEC-430SS	10 m		
		MQDEC-450SS	15 m		
	Male Right-Angle/ Female Straight	MQDEC-403RS	1 m	 	
		MQDEC-406RS	2 m		
		MQDEC-412RS	4 m		
		MQDEC-420RS	7 m		
		MQDEC-430RS	10 m		
		MQDEC-450RS	15 m		




4-Pin Euro-Style Splitter Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 22 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Connections				
Pinout	Model	Branches	Trunk	Used With
  1 = Brown 2 = White 3 = Blue 4 = Black	CSB-M1240M1240*	4-Pin Euro QD No Branch Female	No Trunk Male	• Sensors w/4-Pin Euro QD • EZ-LIGHT
	CSB-M1241M1241	4-Pin Euro QD 2 x 0.3 m Female	0.3 m Male	
	CSB-M1248M1241		2.5 m Male	
	CSB-M12415M1241		5.0 m Male	
	CSB-M12425M1241		8.0 m Male	
	CSB-UNT425M1241		8.0 m Unterminated	
Dimensions				
 (Trunk) (Branches)				

* CSB-M1240M1240 replaces model number MDCVB4T.




5-Pin Euro-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray	Straight	MQDC1-501.5	0.5 m		• MINI-BEAM <i>Expert</i> • QS30 • PicoDot • Q45 Laser Retro • R55F • SL30 & SL30E • SL10 & SL10E • VTB (2-color) • SLC1 • Q60 • PVD • STB • K50 • K80 • DX80 • DX81 • DX85 • EZ-LIGHT
		MQDC1-515	5 m		
		MQDC1-530	9 m		
	Right-Angle	MQDC1-506RA	2 m		
		MQDC1-515RA	5 m		
		MQDC1-530RA	9 m		



5-Pin Euro-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray	Straight	MQDC20-506	2 m		• High Intensity Area Lights • High Intensity Ring Lights • Sealed Linear Array Lights NOTE: Except stainless steel models
		MQDC20-515	5 m		
		MQDC20-530	9 m		



5-Pin Euro-Style Cables with Stainless Steel Connector

Cable: PVC jacket, PUR (polyurethane) connector body, 316 stainless steel coupling nut

Conductors: 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray	Straight	MQDC20SS-506	2 m		• Sealed High Intensity Area Lights • Sealed Linear Array Lights NOTE: Stainless steel models
		MQDC20SS-515	5 m		
		MQDC20SS-530	9 m		




5-Pin Euro-Style Cables with Shield

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut




Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc



Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray	Straight	MQDEC2-506	2 m		• Q50 • R58E • M-GAGE Q7M • M-GAGE S18M • QT50U dc sensors • S18U • T30U • Q45U • Q45UR • T-GAGE M18T • LX • QT50R
		MQDEC2-515	5 m		
		MQDEC2-530	9 m		
	Right-Angle	MQDEC2-506RA	2 m		
		MQDEC2-515RA	5 m		
		MQDEC2-530RA	9 m		



5-Pin Euro-Style Cables–Double Ended**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut**Conductors:** 22 or 20 AWG high-flex stranded, gold-plated contacts**Voltage Rating:** 250V ac/300V dc**Temperature:** -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
 1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gn/Ye	Female Straight/ Male Straight	DEE2R-51D	0.3 m	 	• MINI-BEAM <i>Expert</i> • QS30 • PicoDot • Q45 Laser Retro • R55F • SL30 & SL30E • SL10 & SL10E • SLC1 • Q60 • PVD • STB • VTB (2-color) • DX85 • DX81
		DEE2R-53D	1.0 m		
		DEE2R-58D	2.4 m		
		DEE2R-515D	4.5 m		
		DEE2R-525D	8.0 m		
		DEE2R-550D	15.0 m		
		DEE2R-575D	23.0 m		
		DEE2R-5100D	30.0 m		

8-Pin Euro-Style Cables with Shield**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut**Conductors:** 22 or 20 AWG high-flex stranded, gold-plated contacts**Voltage Rating:** 250V ac/300V dc**Temperature:** -40° to +90° C



Pinout	Style	Model	Length	Dimensions	Used With
 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Shield	Straight	MQDC-806	2 m		• LT3 • LG5 • LG10
		MQDC-815	5 m		
		MQDC-830	9 m		

8-Pin Euro-Style Cables with Shield**Cable:** PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut**Conductors:** 24 AWG high-flex stranded, gold-plated contacts**Voltage Rating:** 30V ac/36V dc**Temperature:** -40° to +105° C

Pinout	Style	Model	Length	Dimensions	Used With
 1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Blue 8 = Red	Straight	MAQDC-815	5 m		• EZ-ARRAY Emitters/Receivers
		MAQDC-830	9 m		
		MAQDC-850	15 m		




8-Pin Euro-Style Cables with Open-Shield

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut
Conductors: 22 or 20 AWG high-flex stranded, gold-plated contacts
Voltage Rating: 250V ac/300V dc
Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
 Female 1 = White 5 = Gray 2 = Brown 6 = Pink 3 = Green 7 = Blue 4 = Yellow 8 = Red	Straight	MQDC2S-806	2 m		• QC50 • QCX50 • EZ-LIGHT
		MQDC2S-815	5 m		
		MQDC2S-830	9 m		

8-Pin Euro-Style Splitter Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut
Conductors: 22 AWG high-flex stranded, gold-plated contacts
Voltage Rating: 250V ac/300V dc
Temperature: -40° to +90° C


Connections				
Pinout	Model	Branches	Trunk	Used With
Male  Female  1 = Brown 2 = Or/Bk 3 = Orange 4 = White 5 = Black 6 = Blue 7 = Gn/Ye 8 = Violet	CSB-M1280M1280	8-Pin Euro QD No Branch Female	No Trunk Male	• EZ-ARRAY Emitters/Receivers
	CSB-M1281M1281	8-Pin Euro QD 2 x 0.3 m Female	0.3 m Male	
	CSB-M1288M1281		2.5 m Male	
	CSB-M12815M1281		5.0 m Male	
	CSB-M12825M1281		8.0 m Male	
	CSB-UNT825M1281		8.0 m Unterminated	
Dimensions				
 (Trunk) (Branches)				

12-Pin M16 Cable










Cable: PVC jacket, nickel-plated brass coupling nut

Conductors: 22 AWG



Voltage Rating: 250V ac Temperature: -30° to +80° C

Pinout	Style	Model	Length	Dimensions	Used With
1 = White 2 = Brown 3 = Green 4 = Yellow 5 = Gray 6 = Pink 7 = Red 8 = Black 9 = Violet 10 = Gy/Pk 11 = Rd/Bu 12 = Blue	 Female	MQDC-1210ST	3 m		• LT7
		MQDC-1230ST	10 m		

12-Pin QD to DB15

Pinout	Style	Model	Length	Dimensions 12-Pin QD	Dimensions DB15	Used With
Male QD  Male DB15 	Straight/DB15	PPC06	2 m			• <i>Pro</i>
		PPC23	7 m			
	Straight (High-Flex)/DB15	PPC06HF	2 m			
		PPC23HF	7 m			
	Right-Angle/DB15	PPC06RA	2 m			
		PPC10RA	3 m			
		PPC23RA	7 m			
	Right-Angle (High-Flex)/DB15	PPC06RAHF	2 m			
PPC23RAHF		7 m				
Female QD  Male DB15 	Straight/DB15	PPC13S	4 m			• <i>Sealed Pro</i>
		PPC23S	7 m			
	Straight/DB15	P4C06SIM	2 m			• <i>P4</i> to PPSIM with DB15 connector
		P4C23SIM	7 m			
		P4C32SIM	10 m			

12-Pin QD

Pinout	Style	Model	Length	Dimensions	Used With
1 = Yellow 2 = Gray 3 = Orange 4 = Pink 5 = Black 6 = Red 7 = White 8 = Light Blue 9 = Purple 10 = Green 11 = Blue 12 = Brown Shield = Bare Metal	 Female QD	P4C06	2 m		• P4 • PPSIM with terminal strip to P4
		P4C23	7 m		
		P4C32	10 m		
		P4C50	16 m		
		P4C75	23 m		




3-Pin Micro-Style Cables

Cable: PVC jacket, 3 x 22 AWG

Conductors: PUR (polyurethane) body, nickel-plated coupling nut, gold-plated contacts

Voltage/Current Rating: 250V ac/dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Green 2 = Red/Black 3 = Red/White	Straight	MQDC-306	2 m		• MINI-BEAM ac SM2A312 sensors
		MQDC-315	5 m		
		MQDC-330	9 m		
	Right-Angle	MQDC-306RA	2 m		
		MQDC-315RA	5 m		
		MQDC-330RA	9 m		




4-Pin Micro-Style Cables

Cable: PVC jacket, 4 x 22 AWG

Conductors: PUR (polyurethane) body, nickel-plated brass coupling nut, gold-plated contacts

Voltage/Current Rating: 250V ac/dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Red/Black 2 = Red/White 3 = Red 4 = Green	Straight	MQAC-406	2 m		• Q45 ac series (suffix Q1) • S18, M18, T18, Q25, S30, T30 & Q40 ac sensors (suffix Q1) • Q60
		MQAC-415	5 m		
		MQAC-430	9 m		
	Right-Angle	MQAC-406RA	2 m		
		MQAC-415RA	5 m		
		MQAC-430RA	9 m		




5-Pin Micro-Style Cables with Shield

Cable: PVC jacket, 5 x 22 AWG with 22 AWG drain wire

Conductors: PUR (polyurethane) body, nickel-plated brass coupling nut, gold-plated contacts

Voltage Rating: 250V ac/dc, 4.0 A

Temperature: +105° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Yellow 4 = Black 5 = Blue	Straight	MQVR3S-506	2 m		• QT50U ac/dc sensors • EZ-LIGHT ac indicators
		MQVR3S-515	5 m		
		MQVR3S-530	9 m		
	Right-Angle	MQVR3S-506RA	2 m		
		MQVR3S-515RA	5 m		
		MQVR3S-530RA	9 m		



3-Pin Mini-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nylon coupling nut

Conductors: 18 AWG high-flex stranded. PVC insulation, gold-plated contacts

Voltage Rating: 250V ac/300V dc

Temperature: -40° to +80° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 3 = Blue 4 = Black	Straight	MBCC-306	2 m		• Q45
		MBCC-312	4 m		
		MBCC-330	9 m		
	Straight	SMICC-306	2 m		• SMI30 Intrinsically safe dc sensors
		SMICC-312	4 m		
		SMICC-330	9 m		
1=Red/Black 3=Red/White 4=Green	Straight	SM30CC-306	2 m		• SM30 2-wire ac sensors
		SM30CC-312	4 m		



4-Pin Mini-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nylon coupling nut

Conductors: 18 AWG high-flex stranded. PVC insulation, gold-plated contacts

Voltage/Current Rating: 250V ac/300V dc

Temperature: -40° to +80° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black	Straight	MBCC-406	2 m		• Q45 dc sensors (suffix Q) • OMNI-BEAM dc power blocks • SM30 dc sensors • OTB w/solid-state output • STB with solid-state output
		MBCC-412	4 m		
		MBCC-430	9 m		



5-Pin Mini-Style Cables

Cable: PVC jacket, PUR (polyurethane) connector body, nylon coupling nut

Conductors: 18 AWG high-flex stranded, gold-plated contacts

Voltage Rating: 250V ac/300V dc



Temperature: -40° to +90° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow	Straight	MBCC-506	2 m		• Q45 Laser Retro • OMNI-BEAM ac power blocks • OMNI-BEAM dc w/ e/m relay • OTB & LTB w/SPDT relay • Q45 5-wire ac • STB with e/m relay
		MBCC-512	4 m		
		MBCC-530	9 m		





5-Pin Mini-Style Cables with Shield

Cable: PVC jacket, PUR (polyurethane) connector body, nylon coupling nut
Conductors: 18 AWG high-flex stranded, PVC insulation, gold-plated contacts
Voltage Rating: 250V ac/300V dc
Temperature: -40° to +80° C




Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Yellow	Straight	MBCC2-506	2 m		• QT50U • Q45U • Q45UR
		MBCC2-512	4 m		
		MBCC2-530	9 m		

5-Pin Mini-Style Cables with Shield and “Twisted Pair”


Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut
Conductors: 18 AWG high-flex stranded, PVC insulation, gold-plated contacts
Voltage Rating: 250V ac/300V dc
Temperature: -40° to +80° C

Pinout	Style	Model	Length	Dimensions	Used With
Female  1 = Black 2 = Blue 3 = Drain 4 = Brown 5 = White	Straight	QDC-515C	5 m		• MINI-ARRAY • High-Resolution MINI-ARRAY
		QDC-525C	8 m		
		QDC-550C	15 m		
		MAQDC-575C	22 m		
		MAQDC-5100C	30 m		
		MAQDC-5125C	38 m		
		MAQDC-5150C	45 m		


DB9 Communication Cordsets

End View	Style	Model	Length	Dimensions	Used With
Male  Female 	Male DB9/ Female DB9	DB9P06	2 m		• Pro
		DB9P15	5 m		
		DB9P30	9 m		
Female  2 = Transmit (TX) 3 = Receive (RX) 5 = Ground (GRD)	Male DB9/ Female DB9	MASC	2 m		• MINI-ARRAY • High-Resolution MINI-ARRAY


Communication Cordsets

End View	Style	Model	Length	Dimensions	Used With
Male  1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray	Straight	MQDMC-506	2 m		• EZ-ARRAY to INTUSB485-1 USB Serial Adapter
		MQDMC-515	5 m		
		MQDMC-530	9 m		
	Right-Angle	MQDMC-506RA	2 m		
		MQDMC-515RA	5 m		
		MQDMC-530RA	9 m		

















RJ45 Ethernet Cordsets

End View	Style	Model	Length	Dimensions	Used With
Male 	Cat5e Shielded	STP07	2.1 m		• Pro • P4
	Cat5e Crossover Shielded	STPX07			
	Cat5e Shielded	STP25	7.3 m		
	Cat5e Crossover Shielded	STPX25			
	Cat5e Shielded	STPX75	23 m		

BNC Coaxial Video Cordsets

Pinout	Style	Model	Length	Dimensions	Used With
Male 	Video Coaxial with BNC	BNC06	2 m		• Pro • P4
		BNC15	5 m		
		BNC30	9 m		

Pico-Style Field-Wireable Connectors (M8)**Contacts:** Gold-plated, rated 60V ac/dc max., 4 A max.**Cable Diameter:** 4.0 to 5.0 mm**Temperature:** -25° to +70° C**Environmental Rating:** NEMA 6P, IP67

Pinout	Style	Model	Dimensions
	3-Pin Male Straight	FIC-M8M3	
	3-Pin Female Straight	FIC-M8F3	
	3-Pin Male Right-Angle	FIC-M8M3A	
	3-Pin Female Right-Angle	FIC-M8F3A	
	4-Pin Male Straight	FIC-M8M4	
	4-Pin Female Straight	FIC-M8F4	
	4-Pin Male Right-Angle	FIC-M8M4A	
	4-Pin Female Right-Angle	FIC-M8F4A	

BRACKETS

CABLES

RETROREFLECTORS

ENCLOSURES/
LENS SHIELDS

MISCELLANEOUS













Euro-Style Field-Wireable Connectors (M12)

Contacts: Gold-plated; 4-pin models rated 250V ac/dc max., 4 A max.; 5-pin models rated 50V ac/dc max., 4 A max.

Cable Diameter: 4.0 to 5.0 mm

Temperature: -25° to +90° C

Environmental Rating: NEMA 6P, IP67

Pinout	Style	Model	Dimensions
	4-Pin Male Straight	FIC-M12M4	
	4-Pin Female Straight	FIC-M12F4	
	4-Pin Male Right-Angle	FIC-M12M4A	
	4-Pin Female Right-Angle	FIC-M12F4A	
	5-Pin Male Straight	FIC-M12M5	
	5-Pin Female Straight	FIC-M12F5	
	5-Pin Male Right-Angle	FIC-M12M5A	
	5-Pin Female Right-Angle	FIC-M12F5A	

BRACKETS

CABLES

RETROREFLECTORS

ENCLOSURES/
LENS SHIELDS

MISCELLANEOUS