

PRODUCT NO	REMARKS
10044351-001LF	OBSOLETE
10044351-002LF	

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:

(A) HOUSING: BLACK, HIGH TEMPERATURE THERMOPLASTIC
UL94V-0 APPROVED, MAX MATERIAL REGRIND NOT TO EXCEED 25%.


(B) CONTACTS: COPPER ALLOY

2. PLATING SPEC: GOLD OVER NICKEL OVERALL.

3. NORMAL FORCE: ABOVE 35gf MIN AT 2.38mm WORKING HEIGHT.

4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.










RECOMMENDED PCB LAYOUT

www.fciconnect.com			surface ASME Y14.5	tolerance std ASME Y14.5	projection MM
			ANGULAR	LINEAR	size A4
			0° ± 1°	0.X ± 0.25 0.XX ± 0.12 0.XXX ± 0.05	Scale 7:1
Dr	KP TAY	11APR05	TOLERANCES UNLESS OTHERWISE SPECIFIED		ECN S06-0262
Eng	KP TAY	02AUG06			Spec ref -
Chr	KP TAY	02AUG06	Product family		
Appr	JOEY NG	02AUG06			
FCI			title SPIN MOTOR CONNECTOR, SMT, 4 POS		dwg no 10044351
			catalog no		Rev. C
			CUSTOMER		sheet 1 of 2



Copyright FCI.



	title SPIN MOTOR CONNECTOR, SMT, 4 POS catalog no	dwg no 10044351 CUSTOMER	Rev. C sheet 2 of 2