







	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

A	Male 							A
---	--	--	--	--	--	--	--	---

B	  Product Specification Material Insulator : Glass-filled Thermoplastic PBT , UL94V-0,Black Contact : Copper alloy, plating gold flash selective gold Shell : Steel, 1000V Tin Over 50U" min Copper Electrical Contact Resistance : 20 milliohms Max at 1 AMP DC. Insulation Resistance : 1000 megohms at 500 VDC. Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute Current Rating : 3 AMP Voltage Rating : 250 VAC/rms 60Hz Wire Spec : 26 AWG-28 AWG Operating Temperature: -55°C--+105°C							B
---	--	--	--	--	--	--	--	---

C	Cover  Order Code: A-Dx°F xx LP III/Z Contact style: - F - Female S - Male No. of Contacts 09 / 15 / 25 / 37 Standard Quality class III							C
---	--	--	--	--	--	--	--	---

D	 Strain Relief<table><tr><th>Positions</th><th>A</th><th>B</th><th>C</th><th>E</th><th>F</th></tr><tr><td>9</td><td>30.81</td><td>24.99</td><td>16.92</td><td>11.08</td><td>13.10</td></tr><tr><td>15</td><td>39.20</td><td>33.30</td><td>25.25</td><td>19.39</td><td>20.70</td></tr><tr><td>25</td><td>53.04</td><td>47.04</td><td>38.96</td><td>33.24</td><td>33.68</td></tr><tr><td>37</td><td>69.40</td><td>63.50</td><td>55.42</td><td>49.86</td><td>50.30</td></tr></table>							Positions	A	B	C	E	F	9	30.81	24.99	16.92	11.08	13.10	15	39.20	33.30	25.25	19.39	20.70	25	53.04	47.04	38.96	33.24	33.68	37	69.40	63.50	55.42	49.86	50.30	D
Positions	A	B	C	E	F																																	
9	30.81	24.99	16.92	11.08	13.10																																	
15	39.20	33.30	25.25	19.39	20.70																																	
25	53.04	47.04	38.96	33.24	33.68																																	
37	69.40	63.50	55.42	49.86	50.30																																	

E	Without Insulator Support							E
---	---	--	--	--	--	--	--	---

F	Without Insulator Support							F
---	---	--	--	--	--	--	--	---



G	RoHS compliant							G	
	Unit:mm								
	Scale	Free	⑦	Update the dimension &shape of cover	Winnle		Customer-No.		
	TOLERANCE								
	X.	±0.38	⑥	Update the operating temperature	Winnle	Drawn	15.08.2012		Lucas
	X.X	±0.25	⑤	Correct the UL-File number	Winnle	Approved	09.07.2014		Winnle
	X.XX	±0.13	④	Update 17.58& 17.28 into 17.40& 17.10mm	Winnle				
	ASSMANN WSW-No.								
	A-DXF xx LPIII/Z								

H	ASSMANN components Drawing-No. ASS 4891 CO rev07							H
---	--	--	--	--	--	--	--	---

	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--




Female



- NOTES:**
- MATERIAL**
1. Insulator Material: Glass-Filled Thermoplastic PBT, UL 94V-0
 2. Contact Material : Copper alloy
 3. Shell : SPC
 4. Plating : Selective Gold Flash
- ELECTRICAL**
1. Current Rating : 3 AMP
 2. Voltage Rating : 250 V AC/rms 60 Hz
 3. Contact Resistance: 20mΩ max at 1 AMP DC
 4. Insulation Resistance: 1000MΩ at 500 VDC
 5. Withstand Voltage : 1000V AC/rms 60Hz for 1 minute
 6. Wire Spec: 26 AWG-28 AWG
 7. Operating temperature: -55 °C+105°C
- UL E No #E198287

3.05 Clear hole

Cover



Strain Relief

Dimensions						
Positions	A	B	D	E	F	
9	30.61	24.99	16.33	11.08	10.16	
15	39.20	33.30	24.70	19.39	17.78	
25	53.05	47.04	38.40	33.24	30.48	
37	69.40	63.50	54.80	49.86	45.72	

Without Insulator Support

RoHS compliant

Unit: mm

Scale	Free TOLERANCE	Update the dimension & shape of cover		Date		Customer-No.	
		⑥	⑦	05.06.2014	15.08.2012	ASSMANN WSW-No.	
X.	±0.38	Update the operating temperature		03.04.2014	09.07.2014	A-DXF xx LP III/Z	
X.X	±0.25	Correct the UL-File number		07.03.2014			
X.XX	±0.13	Update 17.58&17.28 into 17.40&17.10mm					
DIM	TOL	Update the wire specification		28.06.2013			
X. °	±3°	Add the wire specification		06.03.2013			
X.X°	±1.0°	Modification					
Angle	TOL	Id.					

ASSMANN
components

Drawing-No.

ASS 4891 CO

rev07

Replace

Sheet 2/2