


**P6KE Series**



**Agency Approvals**


| AGENCY | AGENCY FILE NUMBER |
|--------|--------------------|
|        | E128662/E230531    |

**Maximum Ratings and Thermal Characteristics (T<sub>A</sub>=25°C unless otherwise noted)**

| Parameter   | Symbol                            | Value      | Unit |
|---|-----------------------------------|------------|------|
| Peak Pulse Power Dissipation by 10/1000µs Test Waveform (Fig.2) (Note 1)              | P <sub>PPM</sub>                  | 600        | W    |
| Steady State Power Dissipation on Infinite Heat Sink at T <sub>L</sub> =75°C (Fig. 6) | P <sub>D</sub>                    | 5.0        | W    |
| Peak Forward Surge Current, 8.3ms Single Half Sine Wave Unidirectional Only (Note 2)  | I <sub>FSM</sub>                  | 100        | A    |
| Maximum Instantaneous Forward Voltage at 50A for Unidirectional Only (Note 3)         | V <sub>F</sub>                    | 3.5/5.0    | V    |
| Operating Junction and Storage Temperature Range                                      | T <sub>J</sub> , T <sub>STG</sub> | -55 to 175 | °C   |
| Typical Thermal Resistance Junction to Lead   | R <sub>uJL</sub>                  | 20         | °C/W |
| Typical Thermal Resistance Junction to Ambient  | R <sub>uJA</sub>                  | 75         | °C/W |

- Notes:**
1. Non-repetitive current pulse, per Fig. 3 and derated above T<sub>A</sub> = 25°C per Fig. 2.
  2. Measured on 8.3ms single half sine wave or equivalent square wave, duty cycle=4 per minute maximum.
  3. V<sub>F</sub><3.5V for devices of V<sub>BR</sub> ≤ 200V and V<sub>F</sub>< 5.0V for devices of V<sub>BR</sub> ≥ 201V.

**Functional Diagram**



**Description**

The P6KE Series is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.


**Features**

- V<sub>BR</sub> @T<sub>J</sub>=V<sub>BR</sub>@25°C x (1+ α T x (T<sub>J</sub>- 25)) (α T: Temperature Coefficient)
- Glass passivated chip junction in DO-15 Package
- 600W peak pulse capability at 10/1000µs waveform, repetition rate (duty cycles):0.01 %
- Fast response time: typically less than 1.0ps from 0 Volts to BV min
- Excellent clamping capability
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC-61000-4-2 ESD 15kV(Air), 8kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2 (IEC801-2)
- EFT protection of data lines in accordance with IEC 61000-4-4 (IEC801-4)
- Low incremental surge resistance
- Typical I<sub>r</sub> less than 1µA above 13V
- High temperature soldering guaranteed: 260°C/40 seconds / 0.375"/(9.5mm) lead length, 5 lbs., (2.3kg) tension
- Plastic package has underwriters laboratory flammability classification 94V-O
- Matte tin lead-free plated
- Halogen free and RoHS compliant
- 2nd level interconnect is Pb-free per IPC/JEDEC J-STD-609A.01

**Applications**

TVS devices are ideal for the protection of I/O interfaces, V<sub>CC</sub> bus and other vulnerable circuits used in telecom, computer, industrial and consumer electronic applications.



### Electrical Characteristics (T<sub>a</sub>=25°C unless otherwise noted)

| Part Number (Uni) | Part Number (Bi) | Reverse Stand off Voltage V <sub>R</sub> (Volts) | Breakdown Voltage V <sub>BR</sub> (Volts) @ I <sub>T</sub> |        | Test Current I <sub>T</sub> (mA) | Maximum Clamping Voltage V <sub>C</sub> @ I <sub>pp</sub> (V) | Maximum Peak Pulse Current I <sub>pp</sub> (A) | Maximum Reverse Leakage I <sub>R</sub> @ V <sub>R</sub> (μA) | Agency Approval  |
|-------------------|------------------|--|--|--------|----------------------------------|---|--|--|---|
|                   |                  |  | MIN  | MAX    |                                  |   |  |  |   |
| P6KE6.8A          | P6KE6.8CA        | 5.80   | 6.45   | 7.14   | 10                               | 10.5  | 58.1   | 1000   | X   |
| P6KE7.5A          | P6KE7.5CA        | 6.40   | 7.13   | 7.88   | 10                               | 11.3  | 54.0   | 500  | X   |
| P6KE8.2A          | P6KE8.2CA        | 7.02   | 7.79   | 8.61   | 10                               | 12.1  | 50.4   | 200  | X   |
| P6KE9.1A          | P6KE9.1CA        | 7.78   | 8.65   | 9.55   | 1                                | 13.4  | 45.5   | 50   | X   |
| P6KE10A           | P6KE10CA         | 8.55   | 9.50   | 10.50  | 1                                | 14.5  | 42.1   | 10   | X   |
| P6KE11A           | P6KE11CA         | 9.40   | 10.50  | 11.60  | 1                                | 15.6  | 39.1   | 5  | X   |
| P6KE12A           | P6KE12CA         | 10.20  | 11.40  | 12.60  | 1                                | 16.7  | 36.5   | 5  | X   |
| P6KE13A           | P6KE13CA         | 11.10  | 12.40  | 13.70  | 1                                | 18.2  | 33.5   | 1  | X   |
| P6KE15A           | P6KE15CA         | 12.80  | 14.30  | 15.80  | 1                                | 21.2  | 28.8   | 1  | X   |
| P6KE16A           | P6KE16CA         | 13.60  | 15.20  | 16.80  | 1                                | 22.5  | 27.1   | 1  | X   |
| P6KE18A           | P6KE18CA         | 15.30  | 17.10  | 18.90  | 1                                | 25.2  | 24.2   | 1  | X   |
| P6KE20A           | P6KE20CA         | 17.10  | 19.00  | 21.00  | 1                                | 27.7  | 22.0   | 1  | X   |
| P6KE22A           | P6KE22CA         | 18.80  | 20.90  | 23.10  | 1                                | 30.6  | 19.9   | 1  | X   |
| P6KE24A           | P6KE24CA         | 20.50  | 22.80  | 25.20  | 1                                | 33.2  | 18.4   | 1  | X   |
| P6KE27A           | P6KE27CA         | 23.10  | 25.70  | 28.40  | 1                                | 37.5  | 16.3   | 1  | X   |
| P6KE30A           | P6KE30CA         | 25.60  | 28.50  | 31.50  | 1                                | 41.4  | 14.7   | 1  | X   |
| P6KE33A           | P6KE33CA         | 28.20  | 31.40  | 34.70  | 1                                | 45.7  | 13.3   | 1  | X   |
| P6KE36A           | P6KE36CA         | 30.80  | 34.20  | 37.80  | 1                                | 49.9  | 12.2   | 1  | X   |
| P6KE39A           | P6KE39CA         | 33.30  | 37.10  | 41.00  | 1                                | 53.9  | 11.3   | 1  | X   |
| P6KE43A           | P6KE43CA         | 36.80  | 40.90  | 45.20  | 1                                | 59.3  | 10.3   | 1  | X   |
| P6KE47A           | P6KE47CA         | 40.20  | 44.70  | 49.40  | 1                                | 64.8  | 9.4  | 1  | X   |
| P6KE51A           | P6KE51CA         | 43.60  | 48.50  | 53.60  | 1                                | 70.1  | 8.7  | 1  | X   |
| P6KE56A           | P6KE56CA         | 47.80  | 53.20  | 58.80  | 1                                | 77.0  | 7.9  | 1  | X   |
| P6KE62A           | P6KE62CA         | 53.00  | 58.90  | 65.10  | 1                                | 85.0  | 7.2  | 1  | X   |
| P6KE68A           | P6KE68CA         | 58.10  | 64.60  | 71.40  | 1                                | 92.0  | 6.6  | 1  | X   |
| P6KE75A           | P6KE75CA         | 64.10  | 71.30  | 78.80  | 1                                | 103.0   | 5.9  | 1  | X   |
| P6KE82A           | P6KE82CA         | 70.10  | 77.90  | 86.10  | 1                                | 113.0   | 5.4  | 1  | X   |
| P6KE91A           | P6KE91CA         | 77.80  | 86.50  | 95.50  | 1                                | 125.0   | 4.9  | 1  | X   |
| P6KE100A          | P6KE100CA        | 85.50  | 95.00  | 105.00 | 1                                | 137.0   | 4.5  | 1  | X   |
| P6KE110A          | P6KE110CA        | 94.00  | 105.00   | 116.00 | 1                                | 152.0   | 4.0  | 1  | X   |
| P6KE120A          | P6KE120CA        | 102.00   | 114.00   | 126.00 | 1                                | 165.0   | 3.7  | 1  | X   |
| P6KE130A          | P6KE130CA        | 111.00   | 124.00   | 137.00 | 1                                | 179.0   | 3.4  | 1  | X   |
| P6KE150A          | P6KE150CA        | 128.00   | 143.00   | 158.00 | 1                                | 207.0   | 2.9  | 1  | X   |
| P6KE160A          | P6KE160CA        | 136.00   | 152.00   | 168.00 | 1                                | 219.0   | 2.8  | 1  | X   |
| P6KE170A          | P6KE170CA        | 145.00   | 162.00   | 179.00 | 1                                | 234.0   | 2.6  | 1  | X   |
| P6KE180A          | P6KE180CA        | 154.00   | 171.00   | 189.00 | 1                                | 246.0   | 2.5  | 1  | X   |
| P6KE200A          | P6KE200CA        | 171.00   | 190.00   | 210.00 | 1                                | 274.0   | 2.2  | 1  | X   |
| P6KE220A          | P6KE220CA        | 185.00   | 209.00   | 231.00 | 1                                | 328.0   | 1.9  | 1  | X   |
| P6KE250A          | P6KE250CA        | 214.00   | 237.00   | 263.00 | 1                                | 344.0   | 1.8  | 1  | X   |
| P6KE300A          | P6KE300CA        | 256.00   | 285.00   | 315.00 | 1                                | 414.0   | 1.5  | 1  | X   |
| P6KE350A          | P6KE350CA        | 300.00   | 332.00   | 368.00 | 1                                | 482.0   | 1.3  | 1  |   |
| P6KE400A          | P6KE400CA        | 342.00   | 380.00   | 420.00 | 1                                | 548.0   | 1.1  | 1  |   |
| P6KE440A          | P6KE440CA        | 376.00   | 418.00   | 462.00 | 1                                | 602.0   | 1.0  | 1  |   |
| P6KE480A          | P6KE480CA        | 408.00   | 456.00   | 504.00 | 1                                | 658.0   | 0.9  | 1  |   |
| P6KE510A          | P6KE510CA        | 434.00   | 485.00   | 535.00 | 1                                | 698.0   | 0.9  | 1  |   |
| P6KE530A          | P6KE530CA        | 451.00   | 503.50   | 556.50 | 1                                | 725.0   | 0.8  | 1  |   |
| P6KE540A          | P6KE540CA        | 460.00   | 513.00   | 567.00 | 1                                | 740.0   | 0.8  | 1  |   |
| P6KE550A          | P6KE550CA        | 468.00   | 522.50   | 577.50 | 1                                | 760.0   | 0.8  | 1  |   |
| P6KE600A          | P6KE600CA        | 512.00   | 570.00   | 630.00 | 1                                | 828.0   | 0.75   | 1  |   |

For bidirectional type having V<sub>R</sub> of 10 volts and less, the I<sub>R</sub> limit is double.

For parts without A, the V<sub>BR</sub> is ± 10% and V<sub>C</sub> is 5% higher than with A parts


**I-V Curve Characteristics**




- $P_{PPM}$  Peak Pulse Power Dissipation** – Max power dissipation
- $V_r$  Stand-off Voltage** – Maximum voltage that can be applied to the TVS without operation
- $V_{BR}$  Breakdown Voltage** – Maximum voltage that flows through the TVS at a specified test current ( $I_r$ )
- $V_c$  Clamping Voltage** – Peak voltage measured across the suppressor at a specified  $I_{ppm}$  (peak impulse current)
- $I_r$  Reverse Leakage Current** – Current measured at  $V_r$
- $V_f$  Forward Voltage Drop for Uni-directional**

**Ratings and Characteristic Curves** ( $T_A=25^\circ\text{C}$  unless otherwise noted)

**Figure 1 - TVS Transients Clamping Waveform**




**Figure 2 - Peak Pulse Power Rating**




continues on next page.

**Ratings and Characteristic Curves** ( $T_A=25^\circ\text{C}$  unless otherwise noted) (Continued)


**Figure 3 - Pulse Derating Curve**




**Figure 4 - Pulse Waveform**




**Figure 5 - Typical Junction Capacitance Uni-Directional**



**Figure 6 - Steady State Power Derating Curve**




**Figure 7 - Maximum Non-Repetitive Forward Surge Current**



**Soldering Parameters**

|  |                                    |                         |
|--|------------------------------------|-------------------------|
| Reflow Condition                                       |                                    | Lead-free assembly      |
| Pre Heat   | - Temperature Min ( $T_{s(min)}$ ) | 150°C                   |
|  | - Temperature Max ( $T_{s(max)}$ ) | 200°C                   |
|  | - Time (min to max) ( $t_s$ )      | 60 – 180 secs           |
| Average ramp up rate (Liquidus Temp ( $T_L$ ) to peak) |                                    | 3°C/second max          |
| $T_{s(max)}$ to $T_L$ - Ramp-up Rate                   |                                    | 3°C/second max          |
| Reflow   | - Temperature ( $T_L$ ) (Liquidus) | 217°C                   |
|  | - Time (min to max) ( $t_s$ )      | 60 – 150 seconds        |
| Peak Temperature ( $T_p$ )                             |                                    | 260 <sup>+0/-5</sup> °C |
| Time within 5°C of actual peak Temperature ( $t_p$ )   |                                    | 20 – 40 seconds         |
| Ramp-down Rate   |                                    | 6°C/second max          |
| Time 25°C to peak Temperature ( $T_p$ )                |                                    | 8 minutes Max.          |
| Do not exceed  |                                    | 280°C                   |



**Flow/Wave Soldering (Solder Dipping)**

|                           |            |
|---------------------------|------------|
| <b>Peak Temperature :</b> | 265°C      |
| <b>Dipping Time :</b>     | 10 seconds |
| <b>Soldering :</b>        | 1 time     |


**Physical Specifications**

|                 |  |
|-----------------|--|
| <b>Weight</b>   | 0.015oz., 0.4g   |
| <b>Case</b>     | JEDEC DO-204AC (DO-15) molded plastic body over passivated junction. |
| <b>Polarity</b> | Color band denotes the cathode except Bipolar.                       |
| <b>Terminal</b> | Matte Tin axial leads, solderable per JESD22-B102.                   |

**Environmental Specifications**


|                            |             |
|----------------------------|-------------|
| <b>High Temp. Storage</b>  | JESD22-A103 |
| <b>HTRB</b>                | JESD22-A108 |
| <b>Temperature Cycling</b> | JESD22-A104 |
| <b>H3TRB</b>               | JESD22-A101 |
| <b>RSH</b>                 | JESD22-B106 |

**Dimensions**




| Dimensions | Inches |       | Millimeters |      |
|------------|--------|-------|-------------|------|
|            | Min    | Max   | Min         | Max  |
| A          | 1.000  | -     | 25.40       | -    |
| B          | 0.230  | 0.300 | 5.80        | 7.60 |
| C          | 0.028  | 0.034 | 0.71        | 0.86 |
| D          | 0.104  | 0.140 | 2.60        | 3.60 |

**Part Numbering System**



**Part Marking System**



**Packaging**

| Part Number | Component Package | Quantity | Packaging Option | Packaging Specification |
|-------------|-------------------|----------|------------------|-------------------------|
| P6KExxxXX   | DO-204AC          | 4000     | Tape & Reel      | EIA STD RS-296          |
| P6KExxxXX-B | DO-204AC          | 1000     | BULK             | Littelfuse Spec.        |

**Tape and Reel Specification**

