

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS							
		P	LTR	DESCRIPTION			DATE	DWN	APVD
G	14		E1	REV PER ECR 06-005716 & 005726			15MAR06	JR	MS

D

C

B


A

D


C

B

A



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 0.00254 [$.000100$] MIN TIN PER ASTM B-545
- 4 MAX OPERATING TEMP 170°C MAX
- 5 WIRE CROSS SECTION AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
12-10 AWG STRANDED	12-10 AWG STRANDED	NOT CERTIFIED

50	LOOSE PIECE, BOX	8-31122-2
2,500	TAPE MOUNTED, REEL	3-31122-7
-	LOOSE PIECE	31122
QTY	PACKAGE TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-9-93	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK DA PATTERSON 2-9-93				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 2-9-93	NAME TERMINAL, RING TONGUE, BUDGET -			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL	FINISH	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=31122	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 8:1		SHEET 1 of 1	REV E1	