






PART NO. ENG. NO.

02-06-1104	4529-(P901)
02-06-1105	4529-(P901)L
02-06-5117	4529-(P231)
02-06-5118	4529-(P231)L
NOT TOOLED	4529-1(P901)L





LEGEND

4529-*(****)*

BLANK= WITH LOCKING TABS
1=WITHOUT LOCKING TABS

P=PREPLATE
BLANK=POSTPLATE
FINISH CODE

FORM
BLANK=STD. CHAIN
A=REWOUND CHAIN
L=LOOSE



SECT. "A-A"

NOTES:

1. MATERIAL: PHOSPHOR BRONZE
2. FINISH:
901 HOT TIN DIP (.00051)/.000020 MIN.
231 SELECT GOLD PLATE (.00125)/.000050 MIN. IN CONTACT AREA, SELECT TIN.
(.00250)/.000100 MIN. IN CRIMP AREA OVER(.00125)/.000050 MIN. NICKEL OVERALL.
3. PRODUCT SPECIFICATION: PS-02-06
4. PACKAGING SPECIFICATION: NOT AVAILABLE
5. TERMINALS FOR USE WITH (1.57)/.062 DIA. SERIES HOUSINGS AND WILL ACCEPT 18 THRU 24 AWG WIRE WITH (1.52/3.05)/.060/.120 INSULATION DIA.

REVISE NOTE 2 EC NO: UCP2015-0104 DRWN:JDFOX 2014/07/11 CHKD:MKIPPER 2014/07/11 APPR:FSM/JH 2014/07/31	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 8:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
			4 PLACES	± ---	± ---	DRAWN BY GEP	DATE 1987/08/17	TITLE CRIMP TERMINAL, FEMALE .062 DIA., PHOS. BRONZE FOR 18 THRU 24 GA. WIRE molex		
			3 PLACES	± ---	± .005	CHECKED BY	DATE			
			2 PLACES	± 0.13	± .010	RW	1987/08/17			
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE			
			0 PLACE	±		RAS	1987/08/17			
			ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.		SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-4529-*		1 OF 1
			SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						